



WSW PN ①	Length
A-USB31C-40C-100	1000±50
A-USB31C-40C-080	800±40
A-USB31C-40C-050	500±30
A-USB31C-40C-020	200±20

**NOTES :**  
 Test condition:  
 1. 100% Open, Short & Miswire testing

NO.	NAME	Description	QTY	UNIT
③	AL SHELL	Aluminum alloy casing, L:25*W:13.4*H:6.7mm	2	PCS
④	OVERMOLD	45P PVC Black	NA	KG
③	CONNECTOR	USB4.0 Type C Male Connector, Pin: Gold Plated, Shell: Nickel Plated, Without E-mark. Black Insulator	1	PCS
③	CONNECTOR	USB4.0 Type C Male Connector, Pin: Gold Plated, Shell: Nickel Plated, With E-mark. Black Insulator	1	PCS
①	CABLE	USB4 Cable (7/0.105*1C+SP48/0.050T+CU+HM)*8COAX+(7/0.08T*1P+HMAM)*1C+(7/0.08T*1C+CU+HM)*4C+43/0.10TC*1C+F+PAPER+B+PVC Jacket OD:4.8mm +BLACK/GRAY Nylon Mesh OD:5.1mm	1	PCS

G	RoHS compliant Unit: mm	Scale	Free				Date	Name	Description: <b>USB4 Cable</b>	G	
		TOLERANCE					Drawn	13.09.2021			Luca
H		DIM	TOL	②	Update Specification	16.11.2022	Luca	Approved	16.11.2022	Luca	ASSMANN WSW-No. ① A-USB31C-40C-xxx
				①	Update PN	11.11.2021	Luca			Drawing-No.	
				①	Drawn	13.09.2021	Luca			Customer-No.	Sheet 1/1
		Angle	TOL	Id.	Modification	Date	Name				