


① WSW P/N	Length (mm)
AMJU2020-0762-BKB-22	7620 ± 200
AMJU2020-0914-BKB-22	9144 ± 300
AMJU2020-1619-BKB-22	12192 ± 500
AMJU2020-1524-BKB-22	15240 ± 600
AMJU2020-1828-BKB-22	18288 ± 700

PIN ASSIGNMENT			
P1		P2	
1	white	1	
2	orange	2	
3	white	3	
6	green	6	
4	blue	4	
5	white	5	
7	white	7	
8	brown	8	
Shell	Braid	Shell	

NOTES :

- 100% OPEN & SHORT TESTING
- CONDUCTOR RESISTANCE: 5Ω MAX
- INSULATION RESISTANCE: 300V DC/10MΩ MIN
- CAT8 CABLE: 2000Mhz, 25Gbps/40Gbps
- CABLE IMPEDANCE: 100±15Ω
- 802.3bt (POE) standard

③	OVERMOLD	PVC COLOR:BLACK	NA	KG
②	CONNECTOR	RJ45 plug 8P8C Contacts:1u" Gold SHELL:Gold Plated UL94V-2	2	PCS
①	CABLE	CAT8 S/FTP Cable,[22AWG(1/0.65 BC)*1P+AL]*4C+AL+BRAID +BLACK PVC JACKET. OD=8.5±0.3MM.	1	PCS
NO.	NAME	DESCRIPTION	QTY	UNIT

G	RoHS compliant Unit: mm	Scale	Free					Date	Name	Description: Modular Cable	
		TOLERANCE						Drawn	14.11.2022		Luca
H		DIM	TOL	①	Change part number	26.04.2023	Luca			ASSMANN WSW-No. ① AMJU2020-xxxx-BKB-22	
				②	Drawn	14.11.2022	Luca			Drawing-No. ASS 10325 CA	rev01
		Angle	TOL	Id.	Modification	Date	Name			Customer-No.	Sheet 1/1