

Mobile Storage, Fast, Small & Unbreakable

Highlights:

- External interface USB3.2 Type C Compatibility with Smart Phones for Fast, Easy Backup
- Read & Write Speed upto 950MB/s & 900MB/s*
- Built in M.2 Socket 3 (M key) interfaces
- Fast NVMe Solid State Performance in a Portable High Capacity Drive
- 5V Power supply without additional power
- LED status indicator and power indicator
- Aluminium Texture (Metal shell for unbreakable experience)
- Shock Resistance & Drop Protection
- Made in India



Sahasra S102e-SE is USB 3.2 Gen2 Portable Solid State Drive, It's a combination of Sleek Design & High Performance. It provides transfer speed of up to 950 MB/s, that's up to 12x faster than external Hard Drives (HDD). Transfers and Backups of large sized data including 4K Videos & High Resolution photos will be much quicker and faster through your PC & Smartphones. Taking your complete data on-the-go with Sahasra Portable SSD is much easier than earlier HDD's. What's more, This sleek and slim drive features a brushed aluminium finish (metal) and is available in 128GB – 2TB of storage space. To keep your data, secure physically and otherwise, its drop, shock, vibration resistant.

High Performance:

Performance-wise, it has transfer speed of up to 950MB/s and a write speed of up to 950MB/s for better productivity and time saving.

All Major OS Covered:

- Support Microsoft Windows 11, Windows 10, Windows 8.1, Windows 7, Vista, XP
- Supports 1-port USB1.1; USB2.0; USB3.0; USB3.1
- Support Mac OS 10.3 or later versions
- Support Linux kernels 2.5 and above

Universal Connectivity:

Connect it to your system & smartphones using the included USB Type-A to Type-C cable, USB Type C to Type C and it's ready to use

Technical Specifications:

Specifications:	
Available Capacities:	128GB, 256GB, 512GB, 1TB, 2TB
Color:	Grey (Metal Finish)
Dimension (L x W xH):	110 x 39 x 8.6 mm
Weight:	46 g
Interface:	Type-C USB3.1 Gen2 (Backward Compatible with USB 2.0)
Operating Temperature:	0°C to 45°C
Storage Temperature:	-20°C to 70°C
System Requirements:	Windows 7/8/8.1/10/11, MAC OS X 10.3 or later versions
Devices Supported:	PC, Notebook or Macintosh with USB port
Durability:	Water & Dust Resistance
Shock Resistant:	upto 1500 G
Vibrant Resistant:	10-2000 Hz
Operating Voltage:	5V
Warranty:	5 Year Limited Warranty

Ordering Information:

Capacity	Color	Part Code	UPC Code
128GB	Grey	CA227-009	685381879867
256GB	Grey	CA227-010	685381788145
512GB	Grey	CA227-001	685381732025
1TB	Grey	CA227-002	685381968660
2TB	Grey	CA227-003	685381582873

For More Information:

Sahasra Electronics Pvt. Ltd.

129-G, Noida Special Economic Zone
Noida-201305, Uttar Pradesh, India

Email: memory@sahasraelectronics.com

Tel: +91-120-2462782/83



* Read/Write Speed is based on internal testing, Performance may be lower depending on drive capacity, Host device, Usages conditions & other factors