



Part Number : [192050009](#)

Series Number : 19205

Product Category : Splices

Product Description : VersaKrimp Parallel Splice for 1/0 AWG Wire

Status : Active

Engineering Number : H-384

---

## Documents & Resources

### Drawings

[Drawing 192050009\\_sd.pdf](#)

### Specifications


[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

### [Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### [EU RoHS Certificate of Compliance](#)

---

## Part Details

### General

Status	Active
Category	Splices
Series	19205
Description	VersaKrimp Parallel Splice for 1/0 AWG Wire
Product Family	Splices
Product Name	Parallel,VersaKrimp
UPC	800755060881

### Agency

CSA	LR18689
UL	E32244

### Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	13.336/g
Packaging Type	Bag
Wire Size (AWG)	1/0

---

## Application Tooling

### Global

Description	Part Number
Manual Putt Pump Hydraulic System, Die set required	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192900011</u>
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	<u>192940008</u>
Hydraulic Dieless Crimping Tool	<u>638161700</u>

Square "Din" Style Die Set for BCL and VersaKrimp Un-insulated Ring Tongue Terminals and Splices, 1/0 and 2/0 AWG	<u>640038070</u>
--	------------------

---

This document was generated on Apr 10, 2024