

Detail	Digi-Key Part Number	Digi-Key Description	Mfg Number	Qty
1	P10GCT-ND	RES SMD 10 OHM 5% 1/10W 0603	ERJ-3GEYJ100V	50
2	P12GCT-ND	RES SMD 12 OHM 5% 1/10W 0603	ERJ-3GEYJ120V	50
3	P15GCT-ND	RES SMD 15 OHM 5% 1/10W 0603	ERJ-3GEYJ150V	50
4	P18GCT-ND	RES SMD 18 OHM 5% 1/10W 0603	ERJ-3GEYJ180V	50
5	P22GCT-ND	RES SMD 22 OHM 5% 1/10W 0603	ERJ-3GEYJ220V	50
6	P27GCT-ND	RES SMD 27 OHM 5% 1/10W 0603	ERJ-3GEYJ270V	50
7	P33GCT-ND	RES SMD 33 OHM 5% 1/10W 0603	ERJ-3GEYJ330V	50
8	P39GCT-ND	RES SMD 39 OHM 5% 1/10W 0603	ERJ-3GEYJ390V	50
9	P47GCT-ND	RES SMD 47 OHM 5% 1/10W 0603	ERJ-3GEYJ470V	50
10	P56GCT-ND	RES SMD 56 OHM 5% 1/10W 0603	ERJ-3GEYJ560V	50
11	P68GCT-ND	RES SMD 68 OHM 5% 1/10W 0603	ERJ-3GEYJ680V	50
12	P82GCT-ND	RES SMD 82 OHM 5% 1/10W 0603	ERJ-3GEYJ820V	50
13	P100GCT-ND	RES SMD 100 OHM 5% 1/10W 0603	ERJ-3GEYJ101V	50
14	P120GCT-ND	RES SMD 120 OHM 5% 1/10W 0603	ERJ-3GEYJ121V	50
15	P150GCT-ND	RES SMD 150 OHM 5% 1/10W 0603	ERJ-3GEYJ151V	50
16	P180GCT-ND	RES SMD 180 OHM 5% 1/10W 0603	ERJ-3GEYJ181V	50
17	P220GCT-ND	RES SMD 220 OHM 5% 1/10W 0603	ERJ-3GEYJ221V	50
18	P270GCT-ND	RES SMD 270 OHM 5% 1/10W 0603	ERJ-3GEYJ271V	50
19	P330GCT-ND	RES SMD 330 OHM 5% 1/10W 0603	ERJ-3GEYJ331V	50
20	P390GCT-ND	RES SMD 390 OHM 5% 1/10W 0603	ERJ-3GEYJ391V	50
21	P470GCT-ND	RES SMD 470 OHM 5% 1/10W 0603	ERJ-3GEYJ471V	50
22	P560GCT-ND	RES SMD 560 OHM 5% 1/10W 0603	ERJ-3GEYJ561V	50
23	P680GCT-ND	RES SMD 680 OHM 5% 1/10W 0603	ERJ-3GEYJ681V	50
24	P820GCT-ND	RES SMD 820 OHM 5% 1/10W 0603	ERJ-3GEYJ821V	50
25	P1.0KGCT-ND	RES SMD 1K OHM 5% 1/10W 0603	ERJ-3GEYJ102V	50
26	P1.2KGCT-ND	RES SMD 1.2K OHM 5% 1/10W 0603	ERJ-3GEYJ122V	50
27	P1.5KGCT-ND	RES SMD 1.5K OHM 5% 1/10W 0603	ERJ-3GEYJ152V	50
28	P1.8KGCT-ND	RES SMD 1.8K OHM 5% 1/10W 0603	ERJ-3GEYJ182V	50
29	P2.2KGCT-ND	RES SMD 2.2K OHM 5% 1/10W 0603	ERJ-3GEYJ222V	50
30	P2.7KGCT-ND	RES SMD 2.7K OHM 5% 1/10W 0603	ERJ-3GEYJ272V	50
31	P3.3KGCT-ND	RES SMD 3.3K OHM 5% 1/10W 0603	ERJ-3GEYJ332V	50
32	P3.9KGCT-ND	RES SMD 3.9K OHM 5% 1/10W 0603	ERJ-3GEYJ392V	50
33	P4.7KGCT-ND	RES SMD 4.7K OHM 5% 1/10W 0603	ERJ-3GEYJ472V	50
34	P5.6KGCT-ND	RES SMD 5.6K OHM 5% 1/10W 0603	ERJ-3GEYJ562V	50
35	P6.8KGCT-ND	RES SMD 6.8K OHM 5% 1/10W 0603	ERJ-3GEYJ682V	50
36	P8.2KGCT-ND	RES SMD 8.2K OHM 5% 1/10W 0603	ERJ-3GEYJ822V	50
37	P10KGCT-ND	RES SMD 10K OHM 5% 1/10W 0603	ERJ-3GEYJ103V	50
38	P12KGCT-ND	RES SMD 12K OHM 5% 1/10W 0603	ERJ-3GEYJ123V	50
39	P15KGCT-ND	RES SMD 15K OHM 5% 1/10W 0603	ERJ-3GEYJ153V	50
40	P18KGCT-ND	RES SMD 18K OHM 5% 1/10W 0603	ERJ-3GEYJ183V	50
41	P22KGCT-ND	RES SMD 22K OHM 5% 1/10W 0603	ERJ-3GEYJ223V	50
42	P27KGCT-ND	RES SMD 27K OHM 5% 1/10W 0603	ERJ-3GEYJ273V	50

43	P33KGCT-ND	RES SMD 33K OHM 5% 1/10W 0603	ERJ-3GEYJ333V	50
44	P39KGCT-ND	RES SMD 39K OHM 5% 1/10W 0603	ERJ-3GEYJ393V	50
45	P47KGCT-ND	RES SMD 47K OHM 5% 1/10W 0603	ERJ-3GEYJ473V	50
46	P56KGCT-ND	RES SMD 56K OHM 5% 1/10W 0603	ERJ-3GEYJ563V	50
47	P68KGCT-ND	RES SMD 68K OHM 5% 1/10W 0603	ERJ-3GEYJ683V	50
48	P82KGCT-ND	RES SMD 82K OHM 5% 1/10W 0603	ERJ-3GEYJ823V	50
49	P100KGCT-ND	RES SMD 100K OHM 5% 1/10W 0603	ERJ-3GEYJ104V	50
50	P120KGCT-ND	RES SMD 120K OHM 5% 1/10W 0603	ERJ-3GEYJ124V	50
51	P150KGCT-ND	RES SMD 150K OHM 5% 1/10W 0603	ERJ-3GEYJ154V	50
52	P180KGCT-ND	RES SMD 180K OHM 5% 1/10W 0603	ERJ-3GEYJ184V	50
53	P220KGCT-ND	RES SMD 220K OHM 5% 1/10W 0603	ERJ-3GEYJ224V	50
54	P270KGCT-ND	RES SMD 270K OHM 5% 1/10W 0603	ERJ-3GEYJ274V	50
55	P330KGCT-ND	RES SMD 330K OHM 5% 1/10W 0603	ERJ-3GEYJ334V	50
56	P390KGCT-ND	RES SMD 390K OHM 5% 1/10W 0603	ERJ-3GEYJ394V	50
57	P470KGCT-ND	RES SMD 470K OHM 5% 1/10W 0603	ERJ-3GEYJ474V	50
58	P560KGCT-ND	RES SMD 560K OHM 5% 1/10W 0603	ERJ-3GEYJ564V	50
59	P680KGCT-ND	RES SMD 680K OHM 5% 1/10W 0603	ERJ-3GEYJ684V	50
60	P820KGCT-ND	RES SMD 820K OHM 5% 1/10W 0603	ERJ-3GEYJ824V	50
61	P1.0MGCT-ND	RES SMD 1M OHM 5% 1/10W 0603	ERJ-3GEYJ105V	50