








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
J5		OBSOLETE PN 178093-3 & 4-178093-1	11NOV2020	PSJ	TM



A-A



B-B



- △ X面から2mmの範囲で測定
- 2 嵌合相手ハウジング型：174516,175442,917992,917978
- 3 推奨取付ねじ
JIS B1115,B1122 タッピングねじ, なべ2種
呼び径3, 長さ6mm以下(締付けトルク: 0.314N・m以下)
- 4 適用製品規格番号：108-5280, 108-5342
- △ 適用製品型番のプリフィックス及びIDマークをカラーホットマークにて表示
- △ 回路番号：下記参照のこと
パワー回路 ① ~ ②
シグナル回路 ③ ~ ③⑧

- △ MUST BE KEPT BETWEEN X AND 2
- 2 THE MATING PLUG HSG. PART NUMBER: 174516,175442,917992,917978
- 3 RECOMMENDED MOUNTING SCREW
3mmDIA,6mmLENGTH(MAX.)PAN HEAD,CLASS 2
TAPPING SCREW SPECIFIED IN JIS B1115,B1122
(TIGHTENING TORQUE:0.314N・m MAX.)
- 4 APPLICABLE PRODUCT .SPEC NO.108-5280, 108-5342
- △ INDICATED PREFIX AND ID MARK OF PRODUCT P/N BY HOT MARK
- △ CIRCUIT NUMBER POWER CIRCUIT NO.①~②
SIGNAL CIRCUIT NO.③~③⑧

54	PRE-TIN x 33 SELECTIVE-TIN [MATTE] SELECTIVE GOLD x 5	⑩ ⑪	②③ ②⑧ ③⑩	NATURAL 自然色	4-5178093-1
53	PRE-TIN x 28 SELECTIVE-TIN [MATTE] SELECTIVE GOLD x 10	④ ⑤ ⑩ ⑪	②③ ②④ ②⑨ ③① ③② ③⑧	NATURAL 自然色	3-5178093-1
52	PRE-TIN x 30 SELECTIVE-TIN [MATTE] SELECTIVE GOLD x 8	④ ⑤ ⑩ ⑪	②③ ②④ ③① ③②	NATURAL 自然色	2-5178093-1
—	PRE-TIN x 18 SELECTIVE-TIN [MATTE] SELECTIVE GOLD x 20	⑦ ⑧ ⑨ ⑩ ⑪ ⑫	②③ ~ ②⑧ ③① ~ ③⑥ ③⑧	NATURAL 自然色	5178093-3
4	PRE-TIN x 33 TIN-LEAD SELECTIVE GOLD x 5	⑩ ⑪	②③ ②④ ③⑥	NATURAL 自然色	4-178093-1
3	PRE-TIN x 28 TIN-LEAD SELECTIVE GOLD x 10	④ ⑤ ⑩ ⑪	②③ ②④ ②⑨ ③① ③② ③⑧	BLACK 黒色	3-178093-2
3	PRE-TIN x 28 TIN-LEAD SELECTIVE GOLD x 10	④ ⑤ ⑩ ⑪	②③ ②④ ②⑨ ③① ③② ③⑧	NATURAL 自然色	3-178093-1
2	PRE-TIN x 30 TIN-LEAD SELECTIVE GOLD x 8	④ ⑤ ⑩ ⑪	②③ ②④ ③① ③②	NATURAL 自然色	2-178093-1
0	PRE-TIN x 38	—	—	ORANGE 橙色	178093-8
—	PRE-TIN x 18 TIN-LEAD SELECTIVE GOLD x 20	⑦ ⑧ ⑨ ⑩ ⑪ ⑫	②③ ~ ②⑧ ③① ~ ③⑥ ③⑧	NATURAL 自然色	178093-3
0	PRE-TIN x 38	—	—	BLACK 黒色	178093-2
0	PRE-TIN x 38	—	—	NATURAL 自然色	178093-1
MARKING マーキング	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	POWER CIRCUIT NO. パワー回路	SIGNAL CIRCUIT NO. シグナル回路	HOUSING COLOR ハウジング色
	CONTACT FINISH コンタクト仕上げ		CIRCUIT NO. OF GOLD PLATED CONTACT 全メッキ端子使用回路番号		P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 純 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	DWN	CHK	APVD	NAME 名称
0 PLC ±	10 ± ±0.2				38Pos.CAP HOUSING ASS'Y
1 PLC ±	30 ± >10 ±0.25				.040/.070 HYBRID I/O CONN.(NON FLANGE TYPE)
2 PLC ±	100 ± >30 ±0.3	PRODUCT SPEC 製品規格			108-5280
3 PLC ±	ANGLE ±3°	APPLICATION SPEC 取付適用規格			—
4 PLC ±		WEIGHT			19.4 g
FINISH 仕上		SIZE	CAGE CODE	DRAWING NO 番号	A2 00779 C=178093
MATERIAL 材料	HOUSING: PBT ハウジング CONTACT: BRASS コンタクト	SEE TABLE		RESTRICTED TO	
				CUSTOMER DRAWING	SCALE 2:1 SHEET 1 of 1 REV J5