



used for: D-SUB COMBINATION

NOTES:

1. METAL SHELLS: STEEL; min. 320µ" TIN
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
4. PLATING: min. 30µ" HARD GOLD OVER min. 50µ" NICKEL
5. = CRITICAL DIMENSION: SPC

Directive 2002/95/EC
RoHS
Compliant

tolerance		scale: 2:1 (5:1)		material: SEE NOTES	
2001	date	name	title:	D-SUB COMBINATION MALE 17W2P SOLDER CUP dwg no: 13K1A405A sh: 1/1 AutoCAD 2000 DIN-A 3 part no: 3017W2PCM99A10X	
drawn	20.11.	Pareil			
appd.	20.11.	Schrader			
norm					
e-old					
DO NOT ALTER CAD DRAWING BY HAND		THIS DRAWING MAY NOT BE COPIED OR		REPRODUCED IN ANY WAY, AND MAY NOT	
OWNERSHIP AND COPYRIGHT OF CONEC GMBH		BE PASSED ON TO A THIRD PARTY WITHOUT		WRITTEN PERMISSION.	
rev.		description		date	
name		name		name	