





PCB LAYOUT

3.5x(N-1)





公差/General tolerances (mm)											D			
0	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400	>500	0.1/10
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	±2

ViVe V



Line greater than 6P, NO slots



2	Pin	Copper Alloy	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

UL 标准/UL Standard:		B	C	D
额定电压/电流/Rated Voltage(V)/Current(A)		300/8	/	300/8
IEC 标准/IEC Standard:				
过压类别/Overvoltage Category/污染等级/Pollution Degree		III/3	III/2	II/2
额定电压/电流/Rated Voltage(V)/Current(A)		/	/	250/12
额定脉冲电压(KV)/Rate Impulse Voltage(KV)		/	/	2.5
间距/Pitch(mm)/线数范围/Poles		3.81/N=02~24P		
使用温度范围/Operating temperature(°C)		-40~+105		
符合RoHS环保要求/Conform to RoHS		Yes		
标准颜色编号/Standard color number: PANTONE / RAL		/		

DEGSON		MATERIAL: SURFACE/COLOR:	
APPD: 竺春华	2022.10.09	MAT NO./REV: / 00	MAT STATUS:
CHKD: 袁耀志	2022.10.09	NAME: 15EDGLC-3.5-XXP-1Y-00L(H)	
DRFT: 方哲盛	2022.10.08	DRAWING NO. 200019404	TYPE CUSTOMER DRAWING
REV	ECN	DESCRIPTION	DRFT DATE
00			方哲盛 2022.10.08
④	A3	1/1	5:1

REV	ECN	DESCRIPTION	DRFT	DATE
00			方哲盛	2022.10.08

Transfer or duplication of this document as well as the utilization of its contents without the written consent of DEGSON is prohibited. All rights reserved for patent. 未经授权复制或传播本文件以及未经许可擅自使用其内容均属于侵权行为。DEGSON 保留所有权利。