



未注公差/General Tolerances(mm)		公差/Dimensional Tolerances(mm)	
0	>3	>6	>18
~3	~10	~18	~30
~6	~18	~30	~50
±0.12	±0.18	±0.22	±0.26
		±0.31	±0.37
		±0.57	±0.80
		±1.05	±1.15
		±1.60	±2.20
		±2.50	±2.50
			0.1/1/0
			EZ

REV	ECN	DESCRIPTION	DRAFT	DATE

MATERIAL:	/	SURFACE:	/
MAT NO.:	/	宁波高松电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD	
STATUS:	/	DRAWING NO.:	
APPD:	ZYH 2022.07.14	NAME: DG35S-B-XXP-1Y-00L(H)	
CHKD:	RSS 2022.07.14	DRAFT: /	
DRAFT:	RSS 2022.07.14	TYPE: CUSTOMER DRAWING	
SIZE: A4	1000 (mm)	SCALE: 2:1	SHEET 1/1

ITEM	NAME OF PART	MATERIAL	NOTES
3	Screw	Steel	M3/Ni Plated
2	Pin header	Brass	Sn Plated
1	Housing	PA66	UL94 V-0

UL 标准 /UL Standard:	B	C	D
额定电压/电压/Rated Voltage(V)/Current(A)	300/20	/	300/10
螺丝扭矩/Torque Tightening(N·m/Lb·in)	M3, 0.5/4.4		
绞线范围(硬线和软线)/Wire Range(rigid and flexible)(AWG/mm ²)	22~12/0.5~4.0		
可焊/Pitch(mm)/绞线范围/Poles	8.25/N=02~26P		
剥线长度/Stripping length(mm)	7~8		
使用温度范围/Operating temperature(°C)	-40~+105		
符合RoHS环保要求/Conform to RoHS	Yes		