

1424693

https://www.phoenixcontact.com/pc/products/1424693

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Universal, 4-position, unshielded, Socket straight M12, coding: A, Push-lock spring connection, knurl material: Plastic, external cable diameter 4 mm ... 8 mm

Your advantages

- Time-saving Push-Lock connection: Tool-free connection and disconnection of conductors by opening the contact levers
- · Intuitive connection: Easy assignment of individual litz wires with color-coded and numerical identification of the contact levers
- · Integrated Push-in Technology: Wire rigid and pretreated conductors easily by means of simple, direct insertion
- · Shock- and vibration-resistant connection: Proven spring-cage technology guarantees secure and reliable contacting

Commercial data

Item number	1424693
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BF2CFA
Catalog page	Page 19 (C-2-2019)
GTIN	4055626376202
Weight per piece (including packing)	13.8 g
Weight per piece (excluding packing)	13.8 g
Customs tariff number	85366990
Country of origin	DE



https://www.phoenixcontact.com/pc/products/1424693



Technical data

Notes

Assembly instruction: NOTE: Observe the permissible bending radii when laying conductors, since the degree of protection may be put in jeopardy if the bending forces are too high. Alleviate mechanical loads upstream of the connector, e.g. by using cable ties.
--

Mounting

Assembly instructions	The wires can be connected both with ferrules and without	
	ferrules	

Product properties

Product type	Circular connector (cable-side)
Sensor type	Universal
Number of positions	4
No. of cable outlets	1
Shielded	no
Coding	A
Cable outlet	straight

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Dimensions

Dimensional drawing	
	15 J
Length	58 mm
External dimensions	
Outside diameter	4 mm 8 mm
Housing	
Diameter housing	19 mm

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Material of grip body	PA 6.6
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA 6.6



https://www.phoenixcontact.com/pc/products/1424693

Stripping length of the individual wire



Material for screw connection	Plastic		
Connection data			
Conductor connection			
Connection method	Push-lock spring connection		
Connection cross section	0.14 mm ² 0.75 mm ² (without ferrule)		
	0.08 mm ² 0.5 mm ² (with ferrule)		
	0.14 mm² 0.75 mm² (solid)		
Connection cross section AWG	26 18 (without ferrule)		
	28 20 (with ferrule)		
Stripping length of the individual wire	7 mm		
Tightening torque	0.4 Nm (M12 knurl)		
	0.4 Nm (Connector with coupling sleeve)		
	1.5 Nm (Pressure nut with coupling sleeve)		
Pin assignment			
Contact Color (signal designation) Contact (optional)	1 = BN		
	2 = WH		
	3 = BU		
	4 = BK		
Electrical properties			
Rated surge voltage	2.5 kV		
Contact resistance	≤ 5 mΩ		
Insulation resistance	≥ 100 MΩ		
Nominal voltage U _N	250 V AC		
	250 V DC		
Nominal current I _N	4 A (2 A when using 0.14 mm² conductors)		
Mechanical properties			
Mechanical data			
Insertion/withdrawal cycles	≥ 100		
Connector			
Connection 1			
Head design	Socket		
Head cable outlet	straight		
Head thread type	M12		
Coding	A		
Cable/line			
Signal type/category	Universal		

7 mm



1424693

https://www.phoenixcontact.com/pc/products/1424693

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65	
	IP67	
Ambient temperature (operation)	-40 °C 85 °C (Plug / socket)	

Standards and regulations

M12


Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101

1424693


https://www.phoenixcontact.com/pc/products/1424693



Drawings



Schematic diagram




Pin assignment M12 socket, 4-pos., A-coded, view female side



https://www.phoenixcontact.com/pc/products/1424693



Dimensional drawing



M12 x 1 socket, straight



1424693

https://www.phoenixcontact.com/pc/products/1424693

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/pc/products/1424693

F	п	F	
L	ш		
	п		
L		L	

EAC

Approval ID: RU C-DE.BL08.B.00511

<u>®</u>	UL Listed Approval ID: E221474				
		Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
		250 V	4 A	-	26 - 18

cUL Listed Approval ID: E221474				
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
	250 V	4 A	26 - 18	-

cULus Listed



1424693

https://www.phoenixcontact.com/pc/products/1424693

Classifications

ECLASS

	ECLASS-11.0	27440102		
	ECLASS-12.0	27440116		
	ECLASS-13.0	27440116		
ETIM				
ETIM				
	ETIM 9.0	EC002635		
UNSPSC				
	UNSPSC 21.0	39121400		



1424693

https://www.phoenixcontact.com/pc/products/1424693

Environmental product compliance

Fulfills EU RoHS substance requirements	Yes, No exemptions			
China RoHS				
Environment friendly use period (EFUP)	EFUP-E			
	No hazardous substances above the limits			
EU REACH SVHC				
REACH candidate substance (CAS No.)	No substance above 0.1 wt%			



1424693

https://www.phoenixcontact.com/pc/products/1424693

Accessories

PROT-M12 MS-PA-CHAIN - Screw plug

1430899

https://www.phoenixcontact.com/pc/products/1430899

M12 sealing cap with fixing band, for sensor cables, for free M12 sockets



SAC-4P-100,0-PUR/0,25 - Cable reel

1501692

https://www.phoenixcontact.com/pc/products/1501692



By the meter, Cable reel, PUR halogen-free, black-gray RAL 7021, 4-wire, color single wire: brown, white, blue, black, cable length: $100\ m$



1424693

https://www.phoenixcontact.com/pc/products/1424693

SAC-4P-100,0-PUR/0,34 - Cable reel

1501663

https://www.phoenixcontact.com/pc/products/1501663



By the meter, Cable reel, PUR halogen-free, black-gray RAL 7021, 4-wire, color single wire: brown, white, blue, black, cable length: 100 m

AI 0,25-6 YE - Ferrule

3203024

https://www.phoenixcontact.com/pc/products/3203024



Ferrule, sleeve length: 6 mm, color: yellow



1424693

https://www.phoenixcontact.com/pc/products/1424693

A 0,25-7-Ferrule

3202478

https://www.phoenixcontact.com/pc/products/3202478



Ferrule, color: silver

A 0,34-7-Ferrule

3009202

https://www.phoenixcontact.com/pc/products/3009202



Ferrule, color: silver



1424693

https://www.phoenixcontact.com/pc/products/1424693

A 0,5 - 6 - Ferrule

3200218

https://www.phoenixcontact.com/pc/products/3200218



Ferrule, color: silver

AI 0,5 - 6 WH - Ferrule

3200687

https://www.phoenixcontact.com/pc/products/3200687



Ferrule, sleeve length: 6 mm, color: white



1424693

https://www.phoenixcontact.com/pc/products/1424693

TSD 04 SAC - Torque screwdriver

1208429

https://www.phoenixcontact.com/pc/products/1208429



Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors

SACC BIT M12-D20 - Tool

1208445

https://www.phoenixcontact.com/pc/products/1208445

Nut for assembling M12 connectors for assembly with a knurl diameter of 20 mm, for 4 mm hexagonal drive





1424693

https://www.phoenixcontact.com/pc/products/1424693

TSD-M 1,2NM - Torque screwdriver

1212224

https://www.phoenixcontact.com/pc/products/1212224



Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 0. 3 - 1.2 Nm

TSD-M SAC-BIT ADAPTER - Adapter insert

1212600

https://www.phoenixcontact.com/pc/products/1212600



Adapter bit for TSD-M...torque tools, E6.3-1/4" drive with 4 mm hexagon to accommodate SAC bits



1424693

https://www.phoenixcontact.com/pc/products/1424693

WIREFOX 2,5 - Stripping tool

1212368

https://www.phoenixcontact.com/pc/products/1212368



Stripping tool, for conductors and cables with a conductor cross section from 0. 08 to 2.5 mm, self-adjusting, stripping length adjustable up to 15 mm, cutting capacity up to 6 mm² stranded/1.5 mm² solid

WIREFOX SAC - Stripping tool

1212623

https://www.phoenixcontact.com/pc/products/1212623



Stripping pliers, for halogen-free sensor/actuator cables (SAC cables), with PUR and PVC insulation, from \emptyset of 4.4 to 7 mm, any stripping length



1424693

https://www.phoenixcontact.com/pc/products/1424693

CRIMPFOX 6H - Crimping pliers

1212046

https://www.phoenixcontact.com/pc/products/1212046



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.14 mm^2 ... 6 mm^2 , unlockable pressure lock, lateral entry

Phoenix Contact 2024 © - all rights reserved https://www.phoenixcontact.com

PHOENIX CONTACT GmbH & Co. KG Flachsmarktstraße 8 D-32825 Blomberg +49 (0) 5235-3 00 info@phoenixcontact.com