

Female Headers Pitch 2.54 mm, angled

Double row, height 8.5 mm



SPECIFICATION:

Operating Current (Nom.): 3 A
 Operating Temperature: -40°C to 105°C
 Insulation Resistance (Min.): 1000 MΩ
 Contact Resistance (Max.): 20 mΩ
 Dielectric Strength: 1,000 Vac

MATERIAL:






Material (Housing): PBT
 Flammability Class: UL 94 V-0
 Material (Contact Area): copper alloy, gold plated

HANDLING:

Processing: wave soldering
 Packaging: tray

TOLERANCE:

.X: ± 0.25
 .XX: ± 0.20



Recommended PCB Layout
(PCB TOLERANCE ± 0.05)

Order Information

Identifier:	Version:	No. of Contacts:
BL	W	#
Female header pitch 2.54 mm double row angled	angled	2X2: 2 x 2
		2X3: 2 x 3
		2X4: 2 x 4
		:
		2X40: 2 x 40