

### SPECIFICATION:

Operating Current (Nom.):	1 A
Operating Temperature:	-40°C to 70°C
Insulation Resistance (Min.):	500 MΩ
Contact Resistance (Max.):	30 mΩ
Dielectric Strength:	500 Vac

### MATERIAL:





Material (Terminal):	brass, tin plated
Material (Housing):	steel, front nickel plated and back tin plated
Flammability Class:	UL 94 V-0
Material (Insulation):	PBT
Material (Contact Area):	brass, gold plated

### HANDLING:

Packaging:	tray
------------	------

### TOLERANCE:

.X:	± 0.20
.XX:	± 0.10



### Dimensions

Number of Contacts:	A:	B:	C:
15	30.85	25	16.4
26	39.25	33.25	24.7
44	53.1	47.04	38.52
62	69.4	63.5	54.82

### Order Information

Identifier:	No. of Contacts:	Version:
BU	#	HD
D-Sub High Density Female with solder lugs	15: 15 poles	High Density
	26: 26 poles	
	44: 44 poles	
	62: 62 poles	