




## Quartz Crystal


SMD-version

part no.	12.85675
model	KX – 5T
frequency	32.0 MHz
mode	fundamental
operating temperature	-40° ~ +85°C
frequency tolerance at +25°C	±10 ppm
temperature tolerance -40° ~ +85°C	±15 ppm
load capacitance $C_L$	10 pF
series resistance R1 (ESR) max.	50 Ohm
aging at +25°C (first year) max.	±2 ppm
shunt capacitance $C_0$ max.	3.5 pF
drive level max.	100 µW
contents of reel	1000 pcs.


### Dimensions:




### Suggested soldering pad:



### Reflow soldering condition:



### Tape specification:



reel diameter 178 mm