



CUSTOMER PRINT

PART NUMBER: 13280-18PG-3XX

ASS'Y P/N	GROMMET FIT CABLE O.D.
13280-18PG-321	0.21 - 0.25
13280-18PG-325	0.21 - 0.25
13280-18PG-326	0.26 - 0.30
13280-18PG-330	0.26 - 0.30
13280-18PG-331	0.31 - 0.375

- NOTES:
 1. PARTS TO BE BULK PACKED.
 2. ALL DIMENSIONS ARE REFERENCE ONLY



MATING FACE

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT / INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

CHECKED BY: _____
 APPROVED BY: _____
 DATE: _____

DIMENSIONS IN BRACKET [] ARE METRIC.

A	AN	07-01-08	DRAWING CREATED PER DOR 08-644KL	
REV.	INIT.	DATE	DESCRIPTION	
	AN	06-27-08	ORIG. DRAWN BY: AN DATE: 06-27-08 CHECKED BY: APPROVED BY:	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF CONXALL CORPORATION. UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			601 E. WILDWOOD VILLA PARK, IL 60181	
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16 ▽ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX				
SCALE	SIZE	SHEET	TITLE:	
NTS	B	1 OF 1	CONNECTOR KIT	
FILE:	DIRECTORY:	PART NUMBER:	18-#20 PIN CONTACTS (CRIMP)	
3280-18PG-3XX	SLW	13280-18PG-3XX	MAXI-CON-X	
			STANDARD PRODUCT	
				REV A