

| SPECIFICATIONS              |             |       |  |  |  |
|-----------------------------|-------------|-------|--|--|--|
| PARAMETERS                  | VALUES      | UNITS |  |  |  |
| RATED INPUT POWER           | 0.7         | W     |  |  |  |
| MAX INPUT POWER             | 1.0         | W     |  |  |  |
| IMPEDANCE                   | 8± 15%      | OHM   |  |  |  |
| OUTPUT SPL @ 0.7W/0.1M      |             | dD A  |  |  |  |
| (AVG. 0.8, 1, 1.2, 1.5 kHz) | 94±3        | dBA   |  |  |  |
| DISTORTION (MAX.)           | 5%          | -     |  |  |  |
| RESONANT FREQUENCY          | 500±20%     | Hz    |  |  |  |
| FREQUENCY RANGE             | Fo ~ 14,000 | Hz    |  |  |  |
| HOUSING MATERIAL            | ABS         | -     |  |  |  |
| CONE MATERIAL               | MYLAR       | -     |  |  |  |
| MAGNET MATERIAL             | NdFeB       | -     |  |  |  |
| OPERATING TEMPERATURE       | -25 ~ +60   | °C    |  |  |  |
| WEIGHT                      | 1.7         | grams |  |  |  |


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.


©2003, Projects Unlimited Inc.

| REVISION HISTORY |                           |         |          |  |  |  |
|------------------|---------------------------|---------|----------|--|--|--|
| LTR              | DESCRIPTION               | DATE    | APPROVED |  |  |  |
| -                | RELEASED FROM ENGINEERING | 3/23/16 |          |  |  |  |









## NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2011/65/EU COMPLIANT.

| UNLESS OTHERWISE     |          |
|----------------------|----------|
| SPECIFIED:           | SIZE     |
| DIMENSIONS ARE IN    | OIZL     |
| MILLIMETERS,         |          |
| TOLERANCES           | $\Delta$ |
| ARE ±0.5 AND         |          |
| 7.1.1.2 20.0 7.1.1.2 |          |
| ANGLES ARE ±3°.      |          |
| 7.1.1.2 20.0 7.1.1.2 |          |

| NIII |             |           | ΔS01508ΔO-3-R |           |             |           |            |
|------|-------------|-----------|---------------|-----------|-------------|-----------|------------|
|      | M.V.        | 3/23/2016 | M.V.          | 3/23/2016 | B.R.        | 3/23/2016 | 3/23/2016  |
|      | Designed by | Date      | Checked by    | Date      | Approved by | Date      | Drawn Date |

Edition Sheet Speaker 1/1