


SPECIFICATION:

Operating Voltage (Max.):	60 V
Operating Current (Nom.):	3 A
Operating Temperature:	-40°C to 105°C
Insulation Resistance (Min.):	1000 MΩ
Contact Resistance (Max.):	20 mΩ
Operating Life in Mating Cycles (Min.):	200
Dielectric Strength:	500 Vac
Insertion Force (Max.):	3 N
Extraction Force:	1 N



MATERIAL:


Material (Terminal):	brass, tin plated
Material (Housing):	PBT
Flammability Class:	UL 94 V-0
Material (Contact Area):	beryllium copper, gold plated

HANDLING:

Processing:	wave soldering
Packaging:	tube

TOLERANCE:

.X:	± 0.30
.XX:	± 0.20



Order Information

Identifier:	No. of Contacts:	DIP Spacing:	Version:
PZ	#	#	#
IC socket with machined pins	6: 2 x 3	A: 7.62 mm	W: w/o central support (6 - 16 pin)
	8: 2 x 4	B: 10,6 mm	B: with central support
	14: 2 x 7	C: 15.24 mm	
	16: 2 x 8		
	18: 2 x 9		
	20: 2 x 10		
	22: 2 x 11		
	24: 2 x 12		
	28: 2 x 14		
	32: 2 x 16		
	40: 2 x 20		