

Detailed Specifications

| | |
|------------------------------------|--------------------------|
| Frame Width: | 40[mm] |
| Frame Height: | 40[mm] |
| Frame Depth: | 10[mm] |
| Max. Air Flow: | 5.6[CFM] |
| Max. Air Flow: | 0.16[m3 per min] |
| Max. Static Pressure: | 0.15[In H2O] |
| Max. Static Pressure: | 37[Pa] |
| Fan Speed: | 6500[RPM] |
| Noise: | 24.5[dB] |
| Life Expectancy: | 50,000 hours at 40C[L10] |
| Bearing Type: | Ball Bearing |
| Nominal Voltage: | 12[V] |
| Operating Voltage - Lower: | 10.2[V] |
| Operating Voltage - Upper: | 13.8[V] |
| Current: | 0.05[A] |
| Input Power: | 0.6[W] |
| Mass: | 16[g] |
| Tach / Locked Rotor Output: | No |
| Status: | Active |