


REV	DESCRIPTION	DATE	APPR
1	INITIAL RELEASE	9/3/19	SP



NOTES:

1. Cable UL2586 12AWG, UV Resistant
2. MC4 Solar Plug Connector
3. MC4 Solar Jack Connector
4. Shrink Tube, Black, Adhesive Inner Wall

THE COMPONENTS, INCLUDING ANY PLATING OR COATINGS, SUPPLIED PER THIS DRAWING MUST BE COMPLIANT WITH EU DIRECTIVE 2011/65/EC (RoHS2 DIRECTIVE)

Unless Otherwise Specified Dimensions are in INCHES (MM)

TOLERANCES:		
DECIMALS	ANGLES	HOLE DIAMETERS
X.X ± 0.1	X ± 1°	<.1 .1 TO .5 >.5
X.XX ± 0.02	X.X ± 0.5°	+ .003 +.005 +.007
X.XXX ± 0.005	X.XX ± 0.1°	-.001 -.002 -.003



14641 S 800 W Suite A
Bluffdale, UT 84065

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION DATA AND DESIGN CONTAINED HEREIN IS PROPRIETARY AND CONFIDENTIAL TO TYCON SYSTEMS INC. DISCLOSURE TO EMPLOYEES AND/OR THIRD PARTIES SHALL BE ON A NEED TO KNOW BASIS ONLY.

TITLE
Cable Assy, 12AWG, 6.1m, Outdoor Rated, with MC4 solar connectors

DRAWN	DATE	SIZE	DWG NO	REV
		A	RPST-CABLE20-Conn	1
ENGINEER S. Parsons	DATE 9/3/19	Do Not Scale Drawing	COPYRIGHT © 2019 Tycon Systems	SHEET 1 of 1