


REV.	MODIFICATION.	DATE	DRN
01	NEW DRAWING	13/07/04	NJB
02	MATL. DETAILS ADDED	23/09/04	NJB
03	APPLICATION VIEW & SECONDARY DIMS ADDED	04/10/04	NJB
04	ECN 04-228	10/12/04	NJB
05	ECN 05-071	14/06/05	OW
06	ECN 05-098	01/08/05	OW
07	ECN 07-198	14/11/07	SF
08	CO2010350	22/08/08	SF



NOTES:  
 1) STANDARD PACK QUANTITY: 100.  
 2) ALL PRIMARY DIMENSIONS IN mm, ALL SECONDARY DIMENSIONS IN [INCHES].  
 3) MATERIAL:  
 (a) FRAME: ALUMINIUM 1060.(RMS-247)  
 (b) MESH: STAINLESS STEEL 304.(RMS-283)  
 4) FINISH: CLEAN.


INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL CORP. AND MUST NOT BE REPRODUCED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.



METRIC GENERAL TOLERANCES UNLESS OTHERWISE STATED	INCHES GENERAL TOLERANCES UNLESS OTHERWISE STATED	THIRD ANGLE
1 DECIMAL PLACES ±	1 DECIMAL PLACES ±	
2 DECIMAL PLACES ±	2 DECIMAL PLACES ±	
ANGULAR ±1°	ANGULAR ±1°	
MATERIAL: SEE NOTES		

DESCRIPTION:	METAL FILTER FRAME (FAN GUARD)	PART NO.:	SEE TABLE
DRG NO.:	04-075	NPR NO.:	
DRN	NJB	DATE	13/07/04
		CHKD	OW
		DATE	13/07/04
		SCALE	NTS
		SHEET NO.	1 OF 1

FORM NO. 01.45/09



PART NO	DIM "A"	DIM "B"	DIM "C"	DIM "D"
MFF-60	59.2 ± 1.0 [2.33 ± 0.039]	50 [1.969]	R7.5 [0.296]	4.0 ± 1.0 [0.157 ± 0.039]
MFF-80	83.82 ± 1.0 [3.30 ± 0.039]	71.37 [2.810]	R10 [0.394]	3.5 ± 1.0 [0.137 ± 0.039]
MFF-92	92 ± 1.0 [3.63 ± 0.039]	82.5 [3.249]	R12.5 [0.493]	4.0 ± 1.0 [0.157 ± 0.039]
MFF-120	118.87 ± 1.0 [4.68 ± 0.039]	104.77 [4.125]	R25 [0.985]	3.5 ± 1.0 [0.137 ± 0.039]