



Item (Detail view)

4-conductor center terminal block; required between end plate and end terminal block for terminal strips with fixing flanges

Item no.	264-351	GTN / EAN	4044818414740
Content	1 piece	Order unit	piece
Order quantity	100 piece	Increase in order quantity	(100, 200, 300, 400, ...)
Customer item no.		Customs Tariff no.	85369010000
Customs duty for the country of origin	CH	Available	-
List price	On request	Net price	On request
Availability	On request		

Note: Some items may not be available from your local WAGO company. Please note that the quantities ordered in the shopping cart are rounded up to the PU (SPU).

RoHS  Compliant



Article details Approvals Downloads/Certificates Accessories

**Description** 4-conductor center terminal block; required between end plate and end terminal block for terminal strips with fixing flanges

**Remarks**

**Item properties**

Miscellaneous		
Name	Value	Unit
Connection technology	CAGE CLAMP®	
Actuation type	Operating tool	
Connectable conductor materials	Copper	
Solid conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG	
Fine-stranded conductor	0.05 ... 2.5 mm² / 28 ... 12 AWG	
Strip length	8 ... 3 mm / 0.31 ... 0.35 inch	
Total number of connection points	4	
Total number of potentials	1	
Number of levels	1	
Type of wiring	Front-entry wiring	
Note (conductor cross-section)	12 AWG: THHN, THWN	
Width	10 mm / 0.394 in	
Height from the surface	22.1 mm / 0.87 in	
Depth	32 mm / 1.26 in	
Design	horizontal	
Mounting type	Mounting flange	
Marking level	Center marking	
Color	gray	
Fire load [MJ]	0.114	MJ
Weight [g]	6.412	g
Packaging type	BOX	
[mm]	10	mm
Main product function	Through term. block	
Product type	Miniature rail-mount terminal blocks	

Upwards