

2-conductor miniature through terminal block; 2.5 mm<sup>2</sup>; with test option; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®

Item no.	264.711	GTN / EAN	4044818415415
Content	1 piece	Order unit	piece
Order quantity	100 piece	Increase in order quantity	(100, 200, 300, 400, ...)
Customer item no.		Customs Tariff no.	85369010000
Customs duty for the country of origin	CH	Available	-
List price	On request	Net price	On request
Availability	On request		

Note: Some items may not be available from your local WAGO company.  
Please note that the quantities ordered in the shopping cart are rounded up to the PU (SPU).

RoHS   
Compliant



Article details		Approvals	Downloads/Certificates	Accessories
<b>Description</b>				
2-conductor miniature through terminal block; 2.5 mm <sup>2</sup> ; with test option; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®				
<b>Remarks</b>				
<b>Item properties</b>				
<b>Miscellaneous</b>				
<b>Name</b>	<b>Value</b>	<b>Unit</b>		
Connection technology	CAGE CLAMP®			
Actuation type	Operating tool			
Connectable conductor materials	Copper			
Solid conductor	0.08 ... 2.5 mm <sup>2</sup> / 28 ... 12 AWG			
Fine-stranded conductor	0.08 ... 2.5 mm <sup>2</sup> / 28 ... 12 AWG			
Strip length	8 ... 9 mm / 0.31 ... 0.35 Inch			
Total number of connection points	2			
Total number of potentials	1			
Number of levels	1			
Type of wiring	Front-entry wiring			
Nets (conductor cross-section)	15 AWG; 18 AWG; THWN			
Width	6 mm / 0.236 in			
Height from upper-edge of DIN-35 rail	24.5 mm / 0.965 in			
Depth	38 mm / 1.496 in			
Design	horizontal			
Type of mounting	Carrier rail 35 x 15			
Marking level	Carrier marking			
Color	grey			
Fine load [MJ]	0.073	MJ		
Weight [g]	3.878	g		
Package type	BOX			
[mm]	6	mm		
Main product function	Through term. block			
Product type	Miniature rail-mount terminal blocks			

Upwards