



US EU 2-PIN POWER SUPPLY/9W

PARAMETER

PARAMETER	RATED VALUE	ABSOLUTE MAXIMUM
Input Voltage	100-240 VAC	90-264 VAC
Input Frequency	50/60 Hz	47-63 Hz
Input Current (@100-240VAC)	0.4 A	-
Inrush Current (@100-240VAC)	-	40 A
Output Voltage	9 VDC	8.55-9.45 VDC
Output Current	0-1 A	-
Overshoot	5 %	10 %

OTHER PARAMETERS

Short-Circuit protection	V
Input protection	Fuse
HIPOT (Dielectric Withstand Test)	Primary to Secondary: AC3000V
MTBF	50000 h
Input connector	US
Output connector	2-PIN, with cord end terminals
Certification:	UL 60950-1; CSA C22.2 No. 60950-1-07; 47 CFR FCC part 15 subpart B, 10-1-2016; ANSI C63.4:2014; IEC 62321-7-1:2015, IEC 62321-6:2015, IEC 62321-5:2013, IEC 62321-4:2013, IEC 62321:2008 Annex C.

