




PART NO.	DIM. "A"	DIM. "B"
LWS-SR-1-01	.45 (11.4)	.14 (3.6)
LWS-SR-2-01	.65 (16.5)	.34 (8.6)
LWS-SR-3-01	1.03 (26.2)	.72 (18.3)
LWS-SR-4-01	1.31 (33.3)	1.00 (25.4)

USE RICHCO RIVET NO.	FOR CHASSIS THICKNESS
SR-3535	.010-.046 (0.3-1.2)
SR-3545	.046-.081 (1.2-2.1)
SR-3550	.069-.105 (1.8-2.7)
SR-3555	.081-.120 (2.1-3.0)
SR-3560	.109-.144 (2.8-3.7)
SR-3570	.140-.180 (3.6-4.6)
SR-3580	.180-.219 (4.6-5.6)

AS MOLDED POSITION



LOCKED POSITION



NOTES:

- MATERIAL: NYLON 6/6 (RMS-01).  
COLOR: NATURAL.
- FLAME RETARDANT, NYLON (RMS-19).  
COLOR: NATURAL.  
AVAILABLE BY SPECIAL ORDER ONLY.

TITLE: LOCKING WIRE SADDLE, SNAP-RIVET

UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1/2°	FILE # LWSSR	DWN: R.T.	APP:	DWG IN IN (MM)	PRELIMINARY
MAT'L: SEE NOTES	DT: 07/17/01	DT:		PART #	
RE: RICHCO, INC.	RICHCO INC. PO BOX 804238, CHICAGO, 60680 (773) 539-4060			SEE TABLE	PRINT TYPE CA

REV	DESCRIPTION	ENGR	DATE
-----	-------------	------	------

