


## Coaxial PCB Connector 82\_MMBX-S50-0-3/111\_N

### Description

Straight PCB jack

Interface Standards  
SUHNER-MMBX



### Technical Data

#### Electrical Data

Impedance 50 Ω  
Interface frequency max. 12.4 GHz

#### Mechanical Data

Board mounting type surface mount  
Weight 0.0006 kg

#### Environmental Data

Operating temperature -55 °C to 155 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	LCP (Liquid crystal polymer)	

### Related Documents

Outline drawing DOU-00012608  
Catalogue drawing DCA-00012610  
Mounting hole DOU-00012611

### Ordering Information

Tape and Reel package 82\_MMBX-S50-0-3/111\_NM  
Bulk 100 pcs package 82\_MMBX-S50-0-3/111\_NH  
Single package 82\_MMBX-S50-0-3/111\_NE

### Remarks

PCB connector with stand-offs