VUE-2156 Series 15.6" Panel Mount Monitor



Features


- 15.6" active screen size
- 6-axis color adjustment (Green/Red/Blue/Cyan/Magenta/Yellow) for high level and more accuracy customized image
- Full-flat cover glass for extremely simple and elegant surface design
- Anti-glare (AG) treatment on screen for comfortable viewing experience
- Built-in multiple I/O interfaces for diverse media connectivity
- Adopts industrial-grade components for guaranteed performance
- Mount with multi-way and easy to extend peripheral devices (box PC/camera...)
- Front IP65 water-proof rating and IK08 high-level impact protection

(for PCAP touch model)

- Support 10-point touch function (PCAP technology)
- Excellent noise immunity well-suited for rugged applications (CS 10V)
- Support many touch method including fingers, glove, and stylus

Specifications

Model			PCAP touch	None touch
Brand			Advantech	
Display	Active Screen Size		15.6 inch	
	Resolution		1920 x 1080 (FHD)	
	Brightness		450 nits	
	Contrast Ratio		800:1 (Typ.)	
	Aspect Ratio		16:9	
	Viewing Angle		85° / 85° / 85° / 85°	
	Response Time		25 ms (Typ.)	
	Backlight Life (hours)		50,000 (Typ.)	
	Touch Type		Projected Capacitive Touch (PCAP)	N/A
	Touch Function		10 points	N/A
	Touch Interface		USB	N/A
	Todon mondo	Video	VGA x 1, HDMI x 1, DVI-D x 1, DisplayPort x 1	
		Audio	Audio line in x 1	
	Input	Control	USB typeB x 1 (for touch function)	
Connectivity		Others	USB3.0 x 2	
,	Output	Video	N/A	
		Audio	2W+2W Internal Speaker	
		Control	N/A	
Control	OSD Function		Hot key (ON/OFF, LIFT, RIGHT, MENU, AUTO)	
	OSD Language		English, French, Korea, Portuguese, Russian, Simplified Chinese, Spanish, Traditional Chinese	
	Power Type		DC input, 19V Adaptor	
Power	Power Input		100-240V _{AC} , 50-60Hz, 1.5A	
	Power Consumption		24W	
	Operating	Temperature	0°C-+40°C	
Environment		Humidity	10% to 85% (non-condensing)	
	Storage	Temperature	-20°C- +60°C	
	ū .	Humidity	5% to 80% (non-condensing)	
	Housing Material		1.0 mm sheet metal (Black)	
	VESA Compatibility		100 x 100 mm	
Mechanical	Dimensions	Physical	384.80 x 237.10 x 49.04 mm	
Specification	(W x H x D)	Packing	455 x 330 x 185 mm	
	Weight	Net	3.1 Kg	
		Gross	4.7 Kg	
	Mounting on a wall/machine		100 x 100 mm, VESA grid	
Installation	Mounting with stand/arm		100 x 100 mm, VESA grid	
	Mounting through bracket		64 mm, Side mount screw hole	
Approbation	Certificates		CB, UL, BSMI, CCC, CE, UKCA, FCC, CEC, ErP lot5	
Warranty			2-year (1-year for panel)	



Ordering Information

Part Number		Description	Packing List
PCAP touch model	None touch model		
VUE-2156-FD45PA-N4	VUE-2156-FD45MA-N4	Advantech 15.6" Full HD Panel Mount Monitor (incl. Japan, Korea, Australia, and Middle East Power Cord)	 Power Cord (1.5M, Black) Power Adaptor (1.5M, Black) VGA Cable (1.5M, Black) HDMI Cable (1.5M, Black) DisplayPort Cable (1.5M, Black) DVI Cable (1.5M, Black) USB Cable (1.8M, Black), for touch, PCAP model only Audio Cable (1.5M, Black) Side Mount Bracket kit Startup Manual (Paper)
VUE-2156-FD45PC-N4	VUE-2156-FD45MC-N4	Advantech 15.6" Full HD Panel Mount Monitor (incl. China Power Cord)	
VUE-2156-FD45PX-N4	VUE-2156-FD45MX-N4	Advantech 15.6" Full HD Panel Mount Monitor (incl. Europe, Taiwan, UK and US Power Cord)	

Optional Accessories

Part Number	Description
960T-A15DEE-B0	Active Stylus Pen for VUE-2000 series, Black
960T-SD-10H10-L	Desktop Stand for VUE-2000, VESA100x100, Large, support up to 7kg
960T-BT-V2K156	VUE-2156 Bracket kit