

## Detailed Specifications

<b>Frame Width:</b>	92[mm]
<b>Frame Height:</b>	92[mm]
<b>Frame Depth:</b>	38[mm]
<b>Max. Air Flow:</b>	141.2[CFM]
<b>Max. Air Flow:</b>	4[m3 per min]
<b>Max. Static Pressure:</b>	1.02[In H2O]
<b>Max. Static Pressure:</b>	260[Pa]
<b>Fan Speed:</b>	6200[RPM]
<b>Noise:</b>	59[dB]
<b>Life Expectancy:</b>	100,000 hours at 25C[L10]
<b>Bearing Type:</b>	Ball Bearing
<b>Nominal Voltage:</b>	24[V]
<b>Operating Voltage - Lower:</b>	14[V]
<b>Operating Voltage - Upper:</b>	27.6[V]
<b>Current:</b>	0.71[A]
<b>Input Power:</b>	17.04[W]
<b>Mass:</b>	230[g]
<b>Tach / Locked Rotor Output:</b>	Locked Rotor
<b>Status:</b>	Active