



Part Number : [734150780](#)

Product Description : 75 Ohms, MCX Right-Angle Jack, PCB, 1.27µm Gold (Au) Contact Plating, Tray

Series Number : 73415

Status : Active

Product Category : RF / Coaxial Connectors

Documents & Resources

Drawings

[Drawing 734150780_sd.pdf](#)

3D Models and Design Files


[3D Model 734150780_stp.zip](#)

Specifications

[Product Specification PS-89675-183-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73415
Description	75 Ohms, MCX Right-Angle Jack, PCB, 1.27µm Gold (Au) Contact Plating, Tray
Product Family	MCX RF Connectors
Product Name	MCX
Style	PCB
Type	Microminiature
UPC	800756038629

Electrical

Frequency	6 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Gender	Jack
Keying to Mating Part	None
Net Weight	1.685/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Through Hole
PCB Thickness - Recommended	3.20mm
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	1
Max-Temp	260

This document was generated on May 06, 2024