

**MANUFACTURER'S PART NUMBER** GJM022-KIT-TTOL-DE

**KIT DESCRIPTION** 01005 High Q Tight Tolerance

<b>KIT CONTENTS</b>	<b>QTY IN KIT</b>	<b>SPECIFICATIONS</b>
GJM0225C1ER20WB01L	50	01005(0402M) COG 0.20pF ±0.05pF 25V
GJM0225C1ER30WB01L	50	01005(0402M) COG 0.30pF ±0.05pF 25V
GJM0225C1ER40WB01L	50	01005(0402M) COG 0.40pF ±0.05pF 25V
GJM0225C1ER50WB01L	50	01005(0402M) COG 0.50pF ±0.05pF 25V
GJM0225C1ER60WB01L	50	01005(0402M) COG 0.60pF ±0.05pF 25V
GJM0225C1ER70WB01L	50	01005(0402M) COG 0.70pF ±0.05pF 25V
GJM0225C1ER80WB01L	50	01005(0402M) COG 0.80pF ±0.05pF 25V
GJM0225C1ER90WB01L	50	01005(0402M) COG 0.90pF ±0.05pF 25V
GJM0225C1E1R0BB01L	50	01005(0402M) COG 1.0pF ±0.1pF 25V
GJM0225C1E1R1BB01L	50	01005(0402M) COG 1.1pF ±0.1pF 25V
GJM0225C1E1R2BB01L	50	01005(0402M) COG 1.2pF ±0.1pF 25V
GJM0225C1E1R3BB01L	50	01005(0402M) COG 1.3pF ±0.1pF 25V
GJM0225C1E1R4BB01L	50	01005(0402M) COG 1.4pF ±0.1pF 25V
GJM0225C1E1R5BB01L	50	01005(0402M) COG 1.5pF ±0.1pF 25V
GJM0225C1E1R6BB01L	50	01005(0402M) COG 1.6pF ±0.1pF 25V
GJM0225C1E1R7BB01L	50	01005(0402M) COG 1.7pF ±0.1pF 25V
GJM0225C1E1R8BB01L	50	01005(0402M) COG 1.8pF ±0.1pF 25V
GJM0225C1E1R9BB01L	50	01005(0402M) COG 1.9pF ±0.1pF 25V
GJM0225C1E2R0BB01L	50	01005(0402M) COG 2.0pF ±0.1pF 25V
GJM0225C1E2R1BB01L	50	01005(0402M) COG 2.1pF ±0.1pF 25V
GJM0225C1E2R2BB01L	50	01005(0402M) COG 2.2pF ±0.1pF 25V
GJM0225C1E2R3BB01L	50	01005(0402M) COG 2.3pF ±0.1pF 25V
GJM0225C1E2R4BB01L	50	01005(0402M) COG 2.4pF ±0.1pF 25V
GJM0225C1E2R5BB01L	50	01005(0402M) COG 2.5pF ±0.1pF 25V
GJM0225C1E2R6BB01L	50	01005(0402M) COG 2.6pF ±0.1pF 25V
GJM0225C1E2R7BB01L	50	01005(0402M) COG 2.7pF ±0.1pF 25V
GJM0225C1E2R8BB01L	50	01005(0402M) COG 2.8pF ±0.1pF 25V
GJM0225C1E2R9BB01L	50	01005(0402M) COG 2.9pF ±0.1pF 25V
GJM0225C1E3R0BB01L	50	01005(0402M) COG 3.0pF ±0.1pF 25V
GJM0225C1E3R1BB01L	50	01005(0402M) COG 3.1pF ±0.1pF 25V
GJM0225C1E3R2BB01L	50	01005(0402M) COG 3.2pF ±0.1pF 25V
GJM0225C1E3R3BB01L	50	01005(0402M) COG 3.3pF ±0.1pF 25V
GJM0225C1E3R4BB01L	50	01005(0402M) COG 3.4pF ±0.1pF 25V
GJM0225C1E3R5BB01L	50	01005(0402M) COG 3.5pF ±0.1pF 25V
GJM0225C1E3R6BB01L	50	01005(0402M) COG 3.6pF ±0.1pF 25V
GJM0225C1E3R7BB01L	50	01005(0402M) COG 3.7pF ±0.1pF 25V
GJM0225C1E3R8BB01L	50	01005(0402M) COG 3.8pF ±0.1pF 25V
GJM0225C1E3R9BB01L	50	01005(0402M) COG 3.9pF ±0.1pF 25V
GJM0225C1E4R0BB01L	50	01005(0402M) COG 4.0pF ±0.1pF 25V
GJM0225C1E4R1BB01L	50	01005(0402M) COG 4.1pF ±0.1pF 25V
GJM0225C1E4R2BB01L	50	01005(0402M) COG 4.2pF ±0.1pF 25V
GJM0225C1E4R3BB01L	50	01005(0402M) COG 4.3pF ±0.1pF 25V
GJM0225C1E4R4BB01L	50	01005(0402M) COG 4.4pF ±0.1pF 25V

GJM0225C1E4R5BB01L	50	01005(0402M) COG 4.5pF ±0.1pF 25V
GJM0225C1E4R6BB01L	50	01005(0402M) COG 4.6pF ±0.1pF 25V
GJM0225C1E4R7BB01L	50	01005(0402M) COG 4.7pF ±0.1pF 25V
GJM0225C1E4R8BB01L	50	01005(0402M) COG 4.8pF ±0.1pF 25V
GJM0225C1E4R9BB01L	50	01005(0402M) COG 4.9pF ±0.1pF 25V
GJM0225C1E5R0BB01L	50	01005(0402M) COG 5.0pF ±0.1pF 25V
GJM0225C1E5R1BB01L	50	01005(0402M) COG 5.1pF ±0.1pF 25V
GJM0225C1E5R6BB01L	50	01005(0402M) COG 5.6pF ±0.1pF 25V
GJM0225C1E6R0BB01L	50	01005(0402M) COG 6.0pF ±0.1pF 25V
GJM0225C1E6R2BB01L	50	01005(0402M) COG 6.2pF ±0.1pF 25V
GJM0225C1E6R8BB01L	50	01005(0402M) COG 6.8pF ±0.1pF 25V
GJM0225C1E7R0BB01L	50	01005(0402M) COG 7.0pF ±0.1pF 25V
GJM0225C1E7R5BB01L	50	01005(0402M) COG 7.5pF ±0.1pF 25V
GJM0225C1E8R0BB01L	50	01005(0402M) COG 8.0pF ±0.1pF 25V
GJM0225C1E8R2BB01L	50	01005(0402M) COG 8.2pF ±0.1pF 25V
GJM0225C1E9R0BB01L	50	01005(0402M) COG 9.0pF ±0.1pF 25V
GJM0225C1E9R1BB01L	50	01005(0402M) COG 9.1pF ±0.1pF 25V
GJM0225C1E100GB01L	50	01005(0402M) COG 10pF ±2% 25V
GJM0225C1E110GB01L	50	01005(0402M) COG 11pF ±2% 25V
GJM0225C1E120GB01L	50	01005(0402M) COG 12pF ±2% 25V
GJM0225C1E130GB01L	50	01005(0402M) COG 13pF ±2% 25V
GJM0225C1E150GB01L	50	01005(0402M) COG 15pF ±2% 25V
GJM0225C1E160GB01L	50	01005(0402M) COG 16pF ±2% 25V
GJM0225C1E180GB01L	50	01005(0402M) COG 18pF ±2% 25V
GJM0225C1E200GB01L	50	01005(0402M) COG 20pF ±2% 25V
GJM0225C1E220GB01L	50	01005(0402M) COG 22pF ±2% 25V