



Plug Component			Plug Strip Dimension			Wire Spec.	Terminal ROJ & Strip			Terminal Component		
Color	Component	Qty	Strip	ROJ	Color	SVT 18AWGX3C 105°C BLACK  Length: 2000±50 mm	Strip	ROJ	Color	Component	Color	Qty
40P Black 90±5°A	LT-202(10A 125V) (NEMA5-15P)	1	7±1	23±3	Black		7±1	20±3	Black	IEC 320 C13 (LT-511R(10A 125V))	40P BK 90±5°A	1
Nickel-Plated	Plug Terminal	1	7±1	23±3	White		7±1	20±3	White	computer power cord terminals	Copper	3
Nickel-Plated	UL Blades	2	7±1	26±3	Green		7±1	20±3	Green	(511 Inner Body)	White	1
White	(202 Inner Body)	1										

**NOTE :**

1. PLUG : LT-202 AMERICAN TYPE
2. CONNECTOR :
3. CORD : SVT 18AWGX3C 105°C BLACK 2M
4. APPROVALS : UL C-UL
5. Supplier for flexible cord : RHYTHM
6. Hi-Pot Test:2000v/1min<1mA>

**Marking:**

RHYTHM: (UL) E88231 SVT 3X18AWG(0.824mm<sup>2</sup>)  
105°C 300V VW-1 CSA LL54496 SVT  
3X18AWG(0.824mm<sup>2</sup>)105°C 300V VW-1  
RHYTHM R

**Modification History**

DESCRIPTION	DATE

<b>DRAWER</b>	Eric	<b>DATE</b>	20/10/17	<b>P/N</b>	800-18-1-2-SVT0-BL-00200-1
<b>APPROVE</b>		<b>REV.</b>	0	<b>Dr.No.</b>	1091064
		<b>TOL.</b>			±5mm
		<b>ALL DIMENSIONS IN mm</b>			

**CnC Tech**  
Industrial Cable and Connector Technology