




Quartz Crystal


SMD-version

model	KX - K
frequency	11,05920 MHz
mode	fundamental
operating temperature	-20° ~ + 70°C
frequency tolerance at +25°C	± 30 ppm
temperature tolerance at -20° ~ +70°C	± 50 ppm
load capacitance C_L	16 pF
series resonance R_1 max.	50 Ohm
aging at 25°C (first year) max.	± 5 ppm
shunt capacitance C_0 max.	7,0 pF
drive level in mW	0,1
RoHS	according to RoHS 2011/65/EU
contents of reel	1000 pcs.
part no.	12.87802


Dimensions (mm):




Suggested soldering pad:



Reflow soldering condition:



Tape specification:



reel diameter 330 mm