

Mighty Cam ES

Digital Microscope

[22x - 147x] on Post Stand w/ Gooseneck LEDs and 3D Viewer

Digital Inspection and Measurement System featuring our Detented Micro Lens with a 3D Viewer, Mighty Cam ES Camera mounted on post stand with flexible gooseneck LEDs, and includes a 22 inch HD LED Monitor. **Provides a magnification range of 22x to 147x.**



Features


- 3D Viewer allows users to inspect from all angles by simply rotating the viewer
- Micro zoom lens with four detented zoom settings (ideal for accurate and repeatable measurements)
- Mighty Cam ES camera provides excellent image quality in HDMI or USB modes (measurement software included)
- Post stand with adjustable LEDs on flexible goosenecks (LEDs can be positioned where needed for optimal illumination)
- 22" HD Monitor included
- *3D viewer is required to be in the off position to perform measurements

Inspect from Any Angle No need to move the part Micro Zoom Lens 22x - 147x Magnification (22" Monitor)

Mighty Cam
ES


HDMI/USB Camera
designed for quick &
accurate inspection

Gooseneck
LEDs
Position LEDs
for optimal
illumination



HDMI Mode

(Inspect in real-time, capture images, and more without a PC)



Inspect Parts from Any Angle

Mighty Cam ES		
22x-147x on Post Stand w/ Gooseneck LEDs & 3D Viewer		
Item #	26700-151-C05-259-570	
Magnification	3D Viewer ON 22x - 147x (22" Monitor)	3D Viewer OFF 22x - 147x (22" Monitor)
Working Distance	3D Viewer ON 0.91" (23mm)	3D Viewer OFF 3" (76.2mm)
Resolution	Via USB 2.0 1920 x 1080 @ 15FPS	Via HDMI 1920 x 1080 @ 15FPS
Software	Built-in Software Cloud 1.0 ver	PC Software ISCapture
Interface	USB 2.0 & HDMI	
Package Contents	26100-259: Mighty Cam ES 26700-170: 3D Viewer 26700-151-C05: Micro Lens + 0.5x Coupler 16700-151 AP: Lens Adapter Plate 26800B-570: Heavy Duty Post Stand 26800B-517: Focus Mount 26200B-224: Flexible Gooseneck LEDs for Post Stands 26700-406: 22" HDMI LCD Monitor	