



Sample photo

Order symbol: AR16148CHSSLT
Product nbr: 8561076
Description: PC Enclosure
Remarks: Hinged transparent cover w/S.S. Lockable latch

EAN: 6418074066848
EI. number:
Finland:

Including: Hinged cover base with 10-32 brass inserts, latched cover with formed in place PUR gasket, and stainless hinge pin. Quick release latches. (Latch options available.) Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

| Dimensions: | Length | Width | Height | Accessories: |
|-------------------------------------|--------------------------|-------|--------|--|
| mm: | 406 | 356 | 203 | ALBP1614 Aluminum Back Panel |
| inch: | 16.0 | 14.0 | 8.0 | ADFP1614 Dead Front Panel w/ screws |
| Materials: | | | | ASP1614 Aluminum Swing Panel |
| Material: | Polycarbonate | | | ASPK1614 Swing Panel Kit incl. Panel |
| Base colour: | RAL 7035 -light grey | | | ASPHK16 Swing Panel Kit w/o Panel |
| Cover screws material: | Stainless steel | | | AMFL14 14" Mounting Flange Set |
| Cover colour: | Clear transparent | | | |
| Gasket material: | Polyurethane | | | |
| Temperatures: | | | | Rating: |
| Temperature °C (short term): | -40 ... 140 °C | | | Ingress Protection (EN 60529): IP66/IP67 |
| Temperature °C (continuous): | -40 ... 80 °C | | | Impact Resistance (EN 62262): IK09 |
| Temperature °F (short term): | -40 ... 284 °F | | | Electrical insulation: Totally insulated |
| Temperature °F (continuous): | -40 ... 175 °F | | | Halogen free (DIN/VDE 0472, Part 815): 0 |
| Accessories: | | | | UV resistance: UL 508 |
| ABP1614 | Painted Steel Back Panel | | | Flammability Rating: UL 508 |
| | | | | Glow Wire Test (IEC 695-2-1) °C: 960 |
| | | | | NEMA Class: NEMA 4, 4X, 12 and 13 |

