



UNCONTROLLED DOCUMENT

NOTES:
CLAMPING RANGE 2.165 / 2.382



.094±.015

.370±.015

TOLERANCES UNLESS NOTED

- ±.005 ON DIMENSIONS THRU .625
- ±.008 ON DIMENSIONS .626 THRU 1.000
- ±.010 ON DIMENSIONS 1.001 THRU 1.500
- ±.015 ON DIMENSIONS LARGER THAN 1.500
- ±.015 ON FRACTIONAL DIMENSIONS

WE RESERVE THE RIGHT
TO DISCONTINUE ITEMS,
CHANGE SPECIFICATIONS
OR DESIGN AT ANY TIME
WITHOUT NOTICE AND
WITHOUT INCURRING
ANY OBLIGATIONS

PROPERTY OF
MICRO PLASTICS INC.

CATALOG DRAWING
2-1/4" DOUBLE GRIP HOSE CLAMP
MICRO P/N 22DGHC00X
DWG. # 22DGHC00X
FILE SERVER\ENG\WEB

MATERIAL: NYLON 6/6; MOLD BLACK

DATE

SCALE
1:1

TA