



**NOTES:**  
1. SPECIFICATIONS

- Current Rating: 1A AC,DC
  - Voltage Rating: 125V AC,DC
  - Temperature Range: -40°C ~ +105°C
  - Contact Resistance: 20mΩ Max.
  - Insulation Resistance: 100MΩ Min.
  - Withstanding Voltage: 500V AC/minute
  - Material: Natural Thermoplastic, UL94V-0
2. Part number of terminal for wire assembly: 10114827
  3. Ordering Information & Dimensions:

Material: 0: PA66 Natural  
1: PA66 Black  
2: PA66 Yellow  
3: PA66 Natural Glow

LF: See note A

pin counts from 02~15

Packaging: 0: Bulk

Wire Compatible

PART NO.	Dimensions				
	A	B	C	D	E
10114826-x0x02LF	4.25	1.25±0.05	2.95	3.47	3.47
10114826-x0x03LF	5.50	2.50±0.10	4.20	4.72	4.72
10114826-x0x04LF	6.75	3.75±0.10	5.45	5.97	5.97
10114826-x0x05LF	8.00	5.00±0.10	6.70	7.22	7.22
10114826-x0x06LF	9.25	6.25±0.15	7.95	8.47	8.47
10114826-x0x07LF	10.50	7.50±0.15	9.20	9.72	9.72
10114826-x0x08LF	11.75	8.75±0.15	10.45	10.97	10.97
10114826-x0x09LF	13.00	10.00±0.15	11.70	12.22	12.22
10114826-x0x10LF	14.25	11.25±0.20	12.95	13.47	13.47
10114826-x0x11LF	15.50	12.50±0.20	14.20	14.72	14.72
10114826-x0x12LF	16.75	13.75±0.20	15.45	15.97	15.97
10114826-x0x13LF	18.00	15.00±0.20	16.70	17.22	17.22
10114826-x0x14LF	19.25	16.25±0.20	17.95	18.47	18.47
10114826-x0x15LF	20.50	17.50±0.20	19.20	19.72	19.72

mat'l. code		surface	tolerance	projection	product family
ISO 1302	ISO 406	ISO 1109	1109	1109	WTB
tr	ecn no	dr	date	tolerances unless otherwise specified	title
A	T10-0145	JH	12/1/10	0±.25	WTB 1.25MM HOUSING
B	EX-N-23453	TM	03/02/16	.00±.15	
C	EX-N-26408	TONY	03/17/17	.000±	scale 1:1
D	EX-N-27088	TONY	05/24/17		JASON HSU 12/1/10
E	EX-N-30250	TONY	05/23/18		engr Jason Wang 8/18/21
F	EX-N-42077	Jason	08/18/21		Chr -
sheet	revision	F	pppd	Tim Yoo	8/18/21
index	sheet	1			
dwg no					sheet1 of 1
10114826					A3
type					Product Customer Drawing