

Vividia HM-407/410 HDMI/LCD/USB Digital Manual Focus Microscope with 7"/10.1" LCD Screen 4MP Resolution 270x Magnification



Vividia HM-407/410 Multi-Functional HDMI/LCD/USB Digital Microscope combines high-definition image, long object distance, 5 output modes and easy operation together with multi configurations. It supports 4.0MP high sensitivity image sensor, 1080P full HD output, up to 270X magnification with 7"/10.1" TFT-LCD monitor. Perfect for use in the following fields: PCB, mobile/phone maintenance, QC inspection, soldering, repair, educational research, industrial inspection, jewelry & stamp collection, laboratory etc.

Features:

- Long object working distance, good depth of field and high quality images.
- Video of 1080p resolution at 60 fps, no delay at all.
- UV filter, protect the lens from being dirty or damaged during soldering.
- 7/10-inch adjustable screen, 4 MP image sensor, industrial lens, image is very clear and give you great view experience.
- Adjustable stand, the microscope stand can move backward and forward, providing enough soldering working space.
- Outputs to a built-in 7"/10.1" monitor, HDMI to a large TV; USB to a Windows PC, Mac and Chromebook, Android devices

Specifications:

Image sensor: 4 Mega Pixels HD Sensor

Magnification: Up to 270x(HDMI monitor 27 inch)

Video output: UHD 2880X2160 24FPS; FHD1920X1080 60FPS/30FPS, HD1280X720 120FPS

Video format: MP4 Photo

resolution: MAX 4032*3024 (12M 4032*3024)

Photo format: JPG

Output: HDMI, TF card(Not included in the package), USB to a PC

Screen size: 7 inch(HM-407)or 10.1 inch(HM-410)

Compatibility: USB output to Windows 11/10/8/7, Mac and Chromebook

Microscope stand: can move back and forth

Minimum focus distance: 5cm

Power source:5V DC

Stand size: 20cm*12cm*19cm

