

	ſ											
	() Copyri	ght FCI.				$\left(\begin{array}{c} \end{array} \right)$	ry)	1		()	
				1 2			FClconnect.	com				3
	PRODUCT NUMBER	AWG	WIRE BARREL			INSULATION BARREL						
			DIM "A"	DIM "B"	DIM "C"	DIM "D"	DIM "E"	DIM "F"	DIM "L"	DIM "M"		PRODUCT NUMBER
	75967–XY1				OBS	ΟLETE						<u>75967–XYZLF</u>
	75967–XY1LF	28-32	.054/1.37	.058/1.47	.011/0.28	.115/2.92	.105/2.67	.040/1.02	.253/6.42	.697/17.70		
	75967-XY2				0 B S	OLETE						
	75967-XY2LF	22-26	.070/1.78	.070/1.78	.017/0.43	.139/3.53	.120/3.05	.050/1.27	.253/6.42	.697/17.70		
	75967–XY3				0 B S	OLETE						
	75967–XY3LF	18-20	.104/2.64	.104/2.64	.021/0.53	.139/3.53	.120/3.05	.050/1.27	.253/6.42	.697/17.70		BASE
	75967–XY7				UNAVAILABLE							
	75967–XY8	75967-XY8 U N A V A I L A B L E 75967-XY9 U N A V A I L A B L E										
	75967–XY9											
	PLATING CODE		PLATING									
	75967-X1ZLF 3	٥μ"/0.76μ Au IN CONTACT AREA; REMAINDER 3μ"/0.076μ Au FLASH OVER 50μ"/1.27μ Ni										
	75967-X2ZLF 1	5μ"/0.38μ Au IN CONTACT AREA; REMAINDER 3μ"/0.076μ Au FLASH OVER 50μ"/1.27μ Ni										
	75967-X3ZLF 5	75967-X3ZLF 50μ"/1.27μ Au IN CONTACT AREA; REMAINDER 3μ"/0.076μ Au FLASH OVER 50μ"/1.27μ Ni 75967-X6Z 0 B S O L E T E 75967-X6ZLF PRE-PLATED 100μ"/2.54μ TO 160μ"/4.06μ Sn (NOTE 8) 75967-X9ZLF 50μ"/1.27μ Au IN CONTACT AREA; REMAINDER 30μ"/0.76μ Au OVER 50μ"/1.27μ Ni							/1.27µ Ni	NOTES:		
	75967-X6Z								1.	APPLICABLE SPECIFICATI BUS-12-098 PRODUCT		
	75967-X6ZLF P									2	FOR PLATING SPECIFICA	
	75967-X9ZLF 5								Ni		FOR APPLICATION WITH	
											-	CUT-OFF DIMENSION FO
	PACKAGING CODE	FINAL	REELING	QUANTIT	Υ	APPLICATIO	N INFORMA	TION			\smile	MATERIAL: BRASS ASTM

PACKAGING CODE	FINAL REELING	QUANTITY	APPLICATION INFORMATION							
75967-0YZLF	LOOSE PIECE	UNAVAILABLE								
75967-1YZLF	RIGHT TO LEFT	8000 PER REEL	APPLICATOR R. TO L. FEEDING							
75967-3YZLF	LEFT TO RIGHT	8000 PER REEL	APPLICATOR L. TO R. FEEDING							

А

- GS-22-008.
- TO MANUFACTURING SOLDER PROCESSES.
- ALL INTERCONNECT ENVIRONMENTS.

										1		<u> </u>		
				mat	ʻl. cod			surt	face	/ tol(erance	P	roject	ion
					SEE	NOTE	5			\vee			()	
				ltr	ecn n	o dr	date	tole	rances	unless (otherwis	e spe	cifiled	\neg
				Т				0.00	lese	.XX	±.01/.X±.3	3	INCH/	′MN
				U					العام	.XXX ±	±.005/.XX	.±.13		
								0. 7	:2'	.XXXX ±	.0020/.XX	<x±.05< th=""><th>tale</th><th>4:1</th></x±.05<>	tale	4:1
								dr	S.	ROYER	1994-12	2-19		
								engi	Т.	HANNA	1994-12	2-19	Eſ	1
								chr	1	HANNA	1994-12	2-19	1 2	Л
_								арр	d т.	HANNA	1994-12		Ę	Į
B				she	et re	vision								Τ
				inde		leet								
							1 1	•						_
	form: A4mmXLc	1	2								3			

