
1

В

ELCO EUROPE (A DIVISION OF AVX LTD.) CONFIDENTIAL PROPRIETARY
THE DRAWING ON THIS PRINT AND INFORMATION THEREWITH ARE
PROPRIETARY TO ELCO EUROPE (A DIVISION OF AVX LTD.) AND
SHALL NOT BE USED OR DISCUSSED IN WHOLE OR IN PART
WITHOUT ELCO EUROPE'S WRITTEN CONSENT.







## NOTES :-

- I. INSULATION :- WHITE PVC, FLAME RETARDENT VW-I.
- 2. CONDUCTION :- 24AWG, TINNED COPPER, II STRANDS 0.16mmØ.
- 3. NUMBER OF WAYS, SEE TABLE.
- 4. MAXIMUM OPERATING TEMPERATURE 80°C.
- 5. VOLTAGE RATING 300v.
- 6. WIRE TO BE UL2468.
- 7. UL MARKING ON ALTERNATE WIRES.
- 8. SUPPLIED ON REELS, 305m PER REEL

PART NUMBER	NUMBER OF WAYS
90-2220-7360-02-000	2
90-2220-7360-03-000	3
90-2220-7360-04-000	4
90-2220-7360-05-000	5
90-2220-7360-06-000	6

Ø1.50 NOTE I	1.50 PITCH
24AWG NOTE 2	

Elco Europe (A Division of AVX Ltd) CONFIDENTIAL PROPRIETY
The document on this print and information therewith are PROPRIETY
to Elco Europe (A Division of AVX Ltd) and shall not be copied
or disclosed in whole or in part without Elco Europe's written consent.

se No.	Γy	838	0	. 2012	. 20	
Š	$\subseteq$	$\infty$				
0	2	$\tilde{\sim}$	70	80		
_	S	0	_		_	
Re	$\equiv$	_	25	08	$\approx$	

3rd ANGLE
ALL DIMENSIONS
IN MILLIMETRES

© COPYRIGHT ELCO EUROPE
NOT TO BE DISCLOSED OR COPIED
WITHOUT WRITTEN PERMISSION

Drawn N.C.H.	RIBBON CABLE - 24AWG	DATE 25-Jul-12
AV	90-2220-7360-0X-000S	C Issue