NEW PRODUCT BULLETIN


Introducing the **PGSD**


Adjustable Bushings

Features and Benefits

- Converts raw or sharp edged holes into insulated holes
- Locates the cable in the center of the hole and provides some light retention force
- Accommodate cables, wires, tubing or any irregular shaped items
- Flexible internal wings absorb shock and vibration
- Easily snapped into hole with fingertip pressure







Material: UL94 V2 Nylon 6/6, RMS-01* Color: Black								
Part No.	Max. Panel Thickness	Hole Diameter ±.002 (0.05)	Head Diameter "A" ±.020	To Accommodate Bundle Dia. "B" Ref	Overall Height "C" ±.010	"D"	Standard Package	
PGSD-1	.062 (1.57)	.500 (12.7)	.600 (15.2)	.312 (7.9)	.250 (6.4)	.063 (1.6)	500	
PGSD-5	.125 (3.2)				.385 (9.8)	.041 (1)		
PGSD-2	.062 (1.57)	.625 (15.9)	.729 (18.5)	.437 (11.1)	.250 (6.4)	.063 (1.6)		
PGSD-6	.125 (3.2)				.406 (10.3)			
PGSD-3	.062 (1.57)	.750 (19.05)	.844 (21.4)	.500 (12.7)	.250 (6.4)		200	
PGSD-7	.125 (3.2)				.390 (9.9)	.047 (1.2)		
PGSD-4	.062 (1.57)	.875 (22.2)	.937 (23.8)	.560 (14.2)	.250 (6.4)	.063 (1.6)		
PGSD-8	.125 (3.2)	.015 (22.2)			.453 (11.5)			
PGSD-9		1.00 (25.4)	1.063 (27)	.750 (19.1)				
PGSD-10		1.375 (34.9)	1.490 (37.8)	1.00 (25.4)			100	
PGSD-11		1.50 (38.1)	1.609 (40.9)	1.062 (27)	.450 (11.43)	.059 (1.5)	100	
*Available in UL94 VO material by special order. To order, add -VO to the end of the part number								





Heyco Part #	Micro Plastics Part #
2858	
2861	
2862	
2863	
2055	
2077	22AF0625
2089	22AF0750
2119	22AF0875
2137	22AF1000
2184	
2213	
	2858 2861 2862 2863 2055 2077 2089 2119 2137 2184



For free samples, literature or technical assistance, contact our US Headquarters at 800-621-1892

OROHS





Markets

- Electrical
- Telecommunications
- White Goods
- Consumer Electronics
- Point of Purchase

Other Related Richco Product Solutions









www.richco-inc.com