



Specification Sheet: Part# 8368

Neodymium Magnet Disk N35 D1" x 1/32"(A)

Magnet Size:	1" x 1/32"
Tolerances:	±0.004"
Material:	Rare Earth NdFeB
Grade of Neodymium:	N35
Plating/Coating:	Ni-Cu-Ni
Brmax:	11,900Gauss
BHmax:	35 MGOe
Max Temperature:	80°C /176F
Magnetization Direction:	(A)
Surface Gauss:	373.46
Pull Force:	2.34lbs
Magnet Size:	1" x 1/32"

Radial Magnets

www.radialmagnets.com

108 NW 20th Street

Boca Raton, FL 33431

Phone: (561) 392-2103