



Specification Sheet: Part# 8903

Neodymium Magnet Disk N35 D3/8" x 1/4"(A)

Magnet Size: 3/8" x 1/4"
Tolerances: ± 0.004 "
Material: Rare Earth NdFeB
Grade of Neodymium: N35
Plating/Coating: Ni-Cu-Ni(Nickel)
Brmax: 11,900Gauss
BHmax: 35 MGOe
Max Temperature: 80°C /176F
Magnetization Direction: (A)
Surface Gauss: 4,584.89 Gauss
Pull Force: 7.05 lb
Weight: 0.271 oz

Radial Magnets

www.radialmagnets.com

108 NW 20th Street
Boca Raton, FL 33431
Phone: (561) 392-2103