

CHERRY MW 8C ERGO

RECHARGEABLE WIRELESS MOUSE



Models may vary from the image shown

When you place high demands on your ergonomic wireless mouse

Uncompromising quality, exquisite design, the very latest technology and the finest materials: These are the ingredients of the CHERRY MW 8C ERGO wireless mouse. The large, ergonomic form is designed for use with the right hand. Even after hours of intensive work, it still sits comfortably on the mouse. Mouse buttons made of anodized aluminum pamper the hand with their pleasant feel. Comfort is underlined with rubber-padded side sections, with thumb-rest and trendy Voronoi pattern. The thumb automatically finds a pleasant position and can rest relaxed. Large gliding surfaces allow the mouse to move lightly over the desktop, relieving stress from the wrist.

The high-precision sensor allows the wireless mouse to be used on nearly every surface, even on glass tables. Press the DPI button to set the resolution to any of the 4 levels 600, 1000, 1600 or 3200 dpi. This means the mouse is ready for use with high-resolution 4k monitors. The installed rechargeable lithium battery can be simply charged with the supplied USB C cable – even while you work. The generous capacity of 550 mAh means that one charge is enough for several weeks of uninterrupted productivity. A two-color status LED provides the user with information on the battery status, the charging status, the selected resolution or the connection status. Unlike a conventional mouse, the CHERRY MW 8C ERGO can be connected with either the 2.4 GHz wireless USB receiver or Bluetooth®. You can switch connection types quickly using a switch on the base of the mouse without cables. This allows e.g. a laptop to be connected via Bluetooth® and a PC to be connected via a regular wireless connection and both to be operated with the same mouse. Simply press the switch to switch between the two devices. In both cases, the data is transmitted with AES-128 encryption and a long range of over 32 feet.

In addition to this, the CHERRY MW 8C ERGO has a number of other impressive features and subtle details. A highly durable metal mouse wheel, a storage pocket with magnetic latch for the USB receiver as well as a velvety transport pouch. The attention to detail of this wireless mouse leaves nothing to be desired and it is equally suitable for mobile and stationary applications.

Decisive advantages

- Superior handling, especially for right-handed users
- Ideal for medium-sized to large hands
- Thumb rest for fatigue-free working
- Metal surface and mouse wheel
- Rubber-padded sides with trendy Voronoi pattern
- Optionally connected using Bluetooth® or a 2.4 GHz wireless unit – both with AES-128 encryption.
- Highly precise sensor with resolution adjustable in four stages up to 3,200 dpi
- Works on nearly all surfaces, including glass
- Status LED shows low residual battery charge, charging status and resolution
- Lithium battery can be charged via USB-C
- Extra-small nano receiver for wireless operation
- 6 buttons and a scroll wheel
- Includes practical transport pouch

CHERRY MW 8C ERGO

RECHARGEABLE WIRELESS MOUSE

Technical specifications

Mouse

- Resolution: 600/1,000/1,600/3,200 DPI (switchable)
- Sensor: PAW3805EK-CJV1 Glass SEN LGA12
- Number of keys: 6
- Design: Right-handed design

Weights

Mouse:	approx. 4.34 oz
Receiver:	approx. .11 oz
Transport pouch:	approx. .32 oz
USB charging cable:	approx. .74 oz
Total weight (with packaging):	approx. 6.91 oz

Wireless frequency range

Transmission frequency: 2,400 GHz - 2,4835 GHz
Transmission power: max. 10 mW (EIRP)

Reach

Wireless:	approx. 33 ft
Bluetooth®:	approx. 33 ft

Batteries

Rechargeable 550 mAh built-in Li-ion battery

Battery operating time

Up to 70 days with a full battery charge (depending on usage and ambient conditions)

Connection

Wireless, optionally using 2.4 GHz frequency with AES-128 encryption or Bluetooth® 4.0

Connection socket

USB-C socket for charging cable

Product approvals

- CE
- UKCA
- FCC
- China RoHS
- Windows hardware compatibility
- USB IF
- Bluetooth® SIG licensing

System requirements

For connection using Bluetooth®:
Device compatible with min. Bluetooth® 4.0 (low energy)
For connection via USB:
Free USB port, Windows 7, 8, 10, 11

Scope of delivery

- Mouse
- USB wireless receiver
- Transport pouch
- USB charging cable
- Operating instructions

Dimensions

Mouse:	approx. 4.72 x 3.11 x 1.75 in
Receiver:	approx. .75 x .57 x .26 in
Packaging:	approx. 5.28 x 3.62 x 2.24 in

Storage temperature

5 °F to 140 °F, max. 85% humidity

Operating temperature

32 °F to 104 °C, max. 85% humidity

Packaging unit

Number of products in outer package	10
Number of outer packages per pallet	60

Warranty:

We put a lot of dedication and hard work into the development of our products and we are proud of their quality. This is why, in addition to the statutory guarantee mentioned in the operating instructions, we are granting an expanded manufacturer's guarantee that is subject to the conditions stated below.

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase. CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty. Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

CHERRY MW 8C ERGO

RECHARGEABLE WIRELESS MOUSE

Models

	Product name	Order number	Sales Region	Color	EAN/UPC-Code
1	CHERRY MW 8C ERGO	JW-8600	Europe	Black	4025112095702
2	CHERRY MW 8C ERGO	JW-8601	Asia	Black	4025112096471
3	CHERRY MW 8C ERGO	JW-8600US	USA	Black	840183606008

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.