

RKDG D24 WG PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Intelligent cabling solutions can save you valuable time and money.**

The FieldPower® modular system contains the right solution for every cabling task.

Foldable seals for the use of pre-assembled cables

Seals available with M16 and M20 connection thread

Integration of operating and signalling devices into the seal possible

seal possible

General ordering data

Version	FieldPower®, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), RJ45 IP 67 V01 metal moulded crimp, RJ45 IP 67 V01 metal moulded crimp, SF/UTP, PUR, 5 m
Order No.	1069060000
Type	RKDG D24 WG PT6
GTIN (EAN)	4032248827053
Qty.	10 pc(s).

Creation date September 15, 2022 11:27:40 PM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

RKDG D24 WG PT6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	18 mm	Depth (inches)	0.709 inch
Height	33.8 mm	Height (inches)	1.331 inch
Width	46.7 mm	Width (inches)	1.839 inch
Length	5 m	Length (inches)	196.85 inch
Net weight	17.2 g		

Temperatures

Storage temperature	-40 °C...75 °C	Operating temperature	-40 °C...85 °C
---------------------	----------------	-----------------------	----------------

General data

Colour	black	Design	Seal
Halogen	No	Line type	round
Material	EPDM	Mounting position, installation notice	in FieldPower® sealing slot
Protection degree	IP54	Silicone	No
UL 94 flammability rating	HB		

Classifications

ETIM 6.0	EC002624	ETIM 7.0	EC002624
ETIM 8.0	EC002624	ECLASS 9.1	27-18-27-90
ECLASS 10.0	27-18-28-15	ECLASS 11.0	27-18-28-15
ECLASS 12.0	27-18-28-15		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN
Catalogues	Catalogues in PDF-format

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Weidmuller:

1069060000