SPECIFICATIONS


(RoHS Compliant)

 Model Number:
 CR1225-LD12BPL
 Version: 00

 Part Number:
 17002063A
 Aug 30, 2023



Mechanical Drawing:



Motor:

Nominal Voltage = 12 vdcOperating Voltage Range = 10.8 - 13.2 vdcNominal Running Current = 0.28 amps Max. Locked Rotor Current = 0.60 ampsRunning Power = 3.36 watts Average Speed = 3000 RPMBearings = BallAir Flow = 95.6 CFMAcoustic = 51 dBAWeight = 140g

Construction:

Venturi: Plastic, Black, UL 94V-0 Propeller: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 50,000 hours at

Additional Features:

Brushless DC Motor Automatic Restart Capability Electronic Locked Rotor Protection

Polarity Protected

Operating Temperature: -10°C to 70°C

Storage Temperature: -40°C to 85°C

Agencies:

UL,CE

Termination:

250±10mm, 24AWG UL1007 Leadwires

Red = Power(+) Black = Return(-)

PQ Curve:

