



PRODUCT NUMBER	LENGTH L±T
10133304-001LF	200±15
10133304-002LF	500±30



P1, USB MICRO-B PLUG

P2, USB A PLUG

WIRING DIAGRAM



NOTE:

- 100% OPEN/SHORT TEST
- INSULATION RESISTANCE: MIN. 10 MOHMS, TEST AT DC300V, 0.01 SEC
- CONTACT RESISTANCE: 1.0 OHM MAX.

4	OVER MOLD	PVC, BLACK	
3	USB MICRO-B PLUG	HSG: HIGH TEMP. THERMOPLASTIC, BLACK TERMINAL: COPPER ALLOY,GOLD FLASH PLATING	1 pcs
2	USB A PLUG	HSG: HIGH TEMP. THERMOPLASTIC, WHITE TERMINAL: COPPER ALLOY,GOLD FLASH PLATING	1 pcs
1	CABLE	UL2725 USB FLAT CABLE, 28AWG, OD:2.5*5.0mm, PVC, BLACK	
NO.	PART NAME	MATERIAL	QTY.
mat'l. code		surface <input checked="" type="checkbox"/> tolerance	projection
ltr		product family	
ecn no dr date		USB	
A	TAI 2015-06-12	title	
angles		CABLE, USB TYPE A PLUG TO USB MICRO-B PLUG	
line		scale	
dr		KENNY TAI 2015-03-11	
enr		KENNY TAI 2015-03-11	
chr		KENNY TAI 2015-05-13	
appd		PM ZHENG 2015-06-12	
sheet index		revision A	
sheet		1	
		sheet 1 of 1	
		size A4	
		dwg no 10133304	
		type CUSTOMER Drawing	

