



Models may vary from the image shown

With the CHERRY STREAM PROTECT MEMBRANE, millions of CHERRY STREAM KEYBOARD users can now add a customized hygienic key protection membrane to their keyboard.

Together, CHERRY STREAM keyboards and the CHERRY STREAM PROTECT MEMBRANE become CHERRY STREAM PROTECT keyboards. The keypad can be completely wiped cleaned and even disinfected, but is still very comfortable to type on.

CHERRY and ACTIVE KEY - two success stories combining proven quality and hygienic safety in perfect harmony.

The CHERRY brand stands for uncompromising reliability, durability and maximum comfort in daily use. Millions of CHERRY STREAM keyboards have proven their reliability, and not just in everyday office use. Hour after hour, day after day.

ACTIVE KEY has the highest level of expertise as a leading supplier of hygienic input devices. The specialist supplier in the CHERRY Group develops precise fitting and resistant silicone membranes for the highest hygiene standards in clinical applications.

With the STREAM PROTECT MEMBRANE from Active Key, millions of STREAM KEYBOARD users can add a customized hygienic key protection membrane to their keyboard.

Keyboards can harbor dirt and germs, especially with frequent use. The CHERRY STREAM PROTECT KEYBOARD features a flat and completely enclosed key surface that can be easily wiped clean, removing dirt and microorganisms such as bacteria and viruses.

The key membrane can be taken off the keyboard for washing and changing. The STREAM PROTECT MEMBRANE thus effectively protects people, the keyboard and the environment.

The STREAM PROTECT MEMBRANE provides hygienic protection for CHERRY STREAM keyboards in any setting, including public administration, educational institutions, schools and universities, and shared office environments.

## FUNCTION AND PERFORMANCE

- Cleanliness & hygiene: Easy to clean.
- Productive work: Unbeatable typing feel
- Sustainability: Washable, changeable membrane
- Modern design: Slim profile
- Maximum ease of use: 3 integrated status indicators, perfect slip resistance, 10 office & multimedia buttons
- Highest quality: Abrasion-resistant key labeling, Cherry SX scissor mechanism
- Certification: GS mark, 'Blue Angel' eco-label
- Suitable for current STREAM models (JK-85XX / JD-85XX) - not for CHERRY STREAM 3.0

## TECHNICAL DATA

Weight main product:	4 oz
Dimensions product without packaging:	18,23 in x 6,46 in x 0,39 in

Weight of product incl. packaging (g): 10.05 oz

Storage temperature: -4 °F - 140 °F

Working temperature: 32 °F - 140 °F

- Product approvals:
- cURus
  - GS
  - FCC
  - CE
  - UKCA

- Scope of delivery:
- Manual
  - Customer Information
  - Membrane

Application instructions:

- We recommend using nitrile gloves (instead of latex). This reduces the risk of allergies and avoids yellow discoloration of the product due to abrasion of the latex. - Cleaning agents based on mineral oil (e.g. petroleum spirits) must NOT be used for cleaning. - Greasy products such as hand creams or lipid replenishing balms reduce the service life of any silicone product. Regular cleaning will counteract this process.

Cleaning methods:

- Wiping with a soft cloth or a soft brush in combination with soap and water or a commercial dishwashing detergent. - Removing the silicone membrane and separate cleaning with soap and water or a commercially available dishwashing detergent

Warranty: 1 additional year voluntary limited manufacturers warranty

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

EAN & Part number	Color	Layout
4025112106378 61510014	black	EU (USA+ €-Symbol)
4025112106392 61510016	black	DE (Germany)
4025112106415 61510018	black	FR (France)
4025112106439 61510020	black	GB (United Kingdom)
4025112106453 61510022	black	PN (PanNordic)
4025112106477 61510024	black	BE (Belgium)
4025112106491 61510026	black	US (USA)
4025112106385 61510015	white	EU (USA+ €-Symbol)
4025112106408 61510017	white	DE (Germany)
4025112106422 61510019	white	FR (France)
4025112106446 61510021	white	GB (United Kingdom)
4025112106460 61510023	white	PN (PanNordic)
4025112106484 61510025	white	BE (Belgium)
4025112107177 61510027	white	US (USA)

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.