

# G80-11900

Compact keyboard with built-in touchpad



Models may vary from the image shown

The multifunctional TouchBoard is the perfect solution for limited spaces in situations requiring the functions of a 'mouse'. Particularly in hard industrial applications, the CHERRY keyboard shows what she is made of. The model combines outstanding quality with long service life and precise, easy-to-operate touchpad.

## FUNCTION AND PERFORMANCE

- Individual keys with Gold Crosspoint contacts (ML technology)
- Designed for continuous usage - over 20 mill. confirmations per key
- Numeric block with 4 additional, individually inscribable function keys
- High level of reliability and unique precision confirmation feeling
- Programming of alternative key codes e.g. [.] , [,], [00], [000] • Suitable for left and right-handed use

- Additional programming of software macros via the high-performance configuration software 'Cherry Tools'
- Can be used with the standard drivers of the operating system

## TECHNICAL DATA

Weight main product:	35 oz
Dimensions product without packaging:	16,34 in x 7,6 in x 1,46 in
Cable-length:	5.74 ft
Storage temperature:	-4 °F - 140 °F
Working temperature:	32 °F - 122 °F
Product approvals:	<ul style="list-style-type: none"><li>• BSMI</li><li>• CE</li><li>• cURus</li><li>• FCC</li><li>• VCCI</li><li>• VDE</li><li>• China RoHS</li><li>• UKCA</li><li>• ICES-003 (Canada)</li></ul>
Operating system:	<ul style="list-style-type: none"><li>• Windows 7</li><li>• Windows 8</li><li>• Windows 10</li><li>• Windows 11</li></ul>
Scope of delivery:	<ul style="list-style-type: none"><li>• Manual</li><li>• Keyboard</li></ul>
Reliability:	MCBF > 10 Mrd. Betätigungen MTBF > 874.000 Stunden
Software support:	CHERRY KEYS
Service life per key (in million strokes):	50 mio. actuations
Switching characteristics:	linear
Max. current consumption (mA) of keyboard:	36 mA
Keyboard format:	Full-size (100%)
N-key rollover:	not specified
Anti-ghosting:	not specified
Key encryption:	no
Actuating force (cN):	60 cN

Key labeling:	Laser etching
Palm rest:	Palm rest not available
USB hub:	no
Illumination:	no
Adjustable feet:	integrated
Status LEDs:	in housing
Key technology:	Mechanical
Switches:	CHERRY MX BLACK

Keycap material:	ABS
Model number:	MX11900
Warranty:	1 additional year voluntary limited manufacturers warranty

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

EAN & Part number	Switches	Color	Illumination	Layout
4025112045127 G80-11900LTMDE-2	CHERRY MX BLACK	black	no	DE (Germany)
4025112049514 G80-11900LTMEU-2	CHERRY MX BLACK	black	no	EU (USA+ €-Symbol)
4025112055638 G80-11900LTMFR-2	CHERRY MX BLACK	black	no	FR (France)
4025112045134 G80-11900LTMUS-2	CHERRY MX BLACK	black	no	US (USA)
4025112060427 G80-11900LTMXY-0	CHERRY MX BLACK	black	no	
4025112050848 G80-11900LUMBE-2	CHERRY MX BLACK	light-grey	no	BE (Belgium)
4025112050824 G80-11900LUMCH-2	CHERRY MX BLACK	black	no	CH (Switzerland)
4025112049958 G80-11900LUMDE-2	CHERRY MX BLACK	black	no	DE (Germany)
4025112068003 G80-11900LUMES-2	CHERRY MX BLACK	black	no	ES (Spain)
4025112050763 G80-11900LUMEU-2	CHERRY MX BLACK	black	no	EU (USA+ €-Symbol)
4025112077043 G80-11900LUMFA-2	CHERRY MX BLACK	black	no	
4025112050800 G80-11900LUMFR-2	CHERRY MX BLACK	black	no	FR (France)
4025112050787 G80-11900LUMGB-2	CHERRY MX BLACK	black	no	GB (United Kingdom)
4025112087165 G80-11900LUMPN-2	CHERRY MX BLACK	black	no	PN (PanNordic)

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.