

MX-LP 2.1 COMPACT WIRELESS

A colorful trendsetter: the small gaming keyboard for great performance at work too



Models may vary from the image shown

A colorful trendsetter - the CHERRY MX-LP 2.1 Compact Wireless gaming keyboard. Wireless with 3 different modes for high performance when gaming or at work. The compact form with 68 keys has bold color combinations for a timelessly trend-setting appearance.

With CHERRY Advanced Wireless Technology, you can enjoy the full Cherry gaming power even without a cable. You can choose one of three connection modes. Perfect for gaming: interference-free and incredibly fast gaming mode with a latency of less than 1 ms. Multi-use Bluetooth with three channels to switch between multiple devices at the touch of a button. Or you can just use the cable because the intelligent charging technology allows you to play or work even while the keyboard is connected to the USB cable for charging.

It can even put on a show: The impressive RGB lighting in more than 16 million colors and numerous preset color routines are a must. You can also create your own lighting effects and store them directly on the keyboard in its integrated memory. The CHERRY button gives you quick access to the CHERRY gaming software for easy customization of all keyboard settings.

CHERRY MX Low Profile technology gives you uncompromising speed, with quick key recognition

and a shorter bounce time for higher switching frequencies.

The Gold Crosspoint precision switches developed and made in Germany are at the heart of your keyboard. The switches help ensure a lifetime of up to 100 million strokes without loss of input quality.

Cherry standards such as full n-key rollover, anti-ghosting and the WIN key lockout go without saying. The 68 abrasion-resistant keys have caps in a variety of colors. The color scheme varies from model to model. A great choice of colors, as well as the screw-in rubber feet for adjusting the tilt angle, complete the product. Your game - your style - your win.

HIGHLIGHTS

- Wireless 3-mode gaming keyboard with cutting-edge CHERRY MX-LP switches
- Compact keyboard with 68 keys in bold color combinations for a trend-setting appearance
- CHERRY MX Low Profile technology – gold crosspoint precision switches for all keys, developed and made in Germany.
- The switch helps ensure a lifetime of up to 100 million strokes without loss of input quality.
- With a 35% lower profile, 40% higher bounce speed and fast key detection – designed for professional e-sports.
- Equipped with high quality Nordic chip for first-class, consistent performance
- CHERRY Advanced Wireless Technology
- 2.4GHz mode - latency of less than 1ms for ultimate gaming performance
- Bluetooth 5.2 mode - supports three channels for easy switching between multiple devices such as a PC, tablet or smartphone
- Smart charging technology: Type-C cable supports fast charging and allows you to play while the keyboard is charging
- Impressive RGB lighting in more than 16 million colors, with numerous integrated color routines

- Easy light customization: Create and save your own lighting effects in the built-in memory
- Ergonomic comfort thanks to easy height adjustment with the screw-in rubber feet
- Full n-key rollover - all keys are read simultaneously
- Anti-ghosting - no input errors
- WIN key lockout for gaming
- Abrasion-resistant key caps
-

PRODUCT SPECIFICATIONS

Weight main product:	15 oz
Dimensions product without packaging:	12,13 in x 3,9 in x 1,06 in
Cable-length:	5.25 ft
Storage temperature:	-4 °F - 113 °F
Working temperature:	32 °F - 113 °F
Product approvals:	<ul style="list-style-type: none"> • CE • FCC • KCC • SRRC • BQB • EU RoHS
System Requirements-Hardware:	USB-A
Operating system:	<ul style="list-style-type: none"> • Windows 7 • Windows 8 • Windows 10 • Windows 11
Scope of delivery:	<ul style="list-style-type: none"> • Keyboard • Manual • Dongle • USB-A to USB-C Cable
Reliability:	NA
Software support:	CHERRY Utility Software & Assistant
USB dongle:	yes
2.4 Ghz wireless connection:	yes

Encryption in wireless mode:	yes
Wireless range (m):	33 ft
Latency:	1.00 ms
Connection via Bluetooth:	yes
Encryption in Bluetooth mode:	yes
Bluetooth protocol:	Bluetooth 5.2
Bluetooth range (m):	33 ft
Number of batteries:	1
Battery type:	Li-Ion
Battery design:	AAA
Battery rechargeable:	yes
Battery replaceable:	no
Service life per key (in million strokes):	100 mio. actuations
Max. current consumption (mA) of keyboard:	500 mA
Keyboard format:	Compact (65%)
Integrated metal plate:	yes
N-key rollover:	N-Key Rollover
Anti-ghosting:	yes
Response time:	1 ms
Key labeling:	Laser etching + UV coating
Palm rest:	Palm rest not available
USB hub:	no
Adjustable feet:	yes
Status LEDs:	in keys
Key technology:	Mechanical
Keycap material:	ABS
Sealing:	no
Model number:	G80-386A
Convenient exchange:	no
Gasket:	no
Warranty:	2 years warranty

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

Actual battery life is strongly depending on individual user behavior and hardware setup.

EAN & Part number	Switches	Color	Illumination	Layout
4025112100031 G80-3860LYAEU-2	CHERRY MX LOW PROFILE RED	black	RGB	EU (USA+ €-Symbol)
4025112104770 G80-3860LYAKR-2	CHERRY MX LOW PROFILE RED	black	RGB	KR (Korea)
4025112106798 G80-3860LVADE-2	CHERRY MX LOW PROFILE SPEED	black	RGB	DE (Germany)
4025112100048 G80-3860LVAEU-2	CHERRY MX LOW PROFILE SPEED	black	RGB	EU (USA+ €-Symbol)
4025112106811 G80-3860LVAFR-2	CHERRY MX LOW PROFILE SPEED	black	RGB	FR (France)
4025112106835 G80-3860LVAGB-2	CHERRY MX LOW PROFILE SPEED	black	RGB	GB (United Kingdom)
4025112106774 G80-3860LVAUS-2	CHERRY MX LOW PROFILE SPEED	black	RGB	US (USA)
4025112100055 G80-3860LYAEU-17	CHERRY MX LOW PROFILE RED	khaki	RGB	EU (USA+ €-Symbol)
4025112104794 G80-3860LYAKR-17	CHERRY MX LOW PROFILE RED	khaki	RGB	KR (Korea)
4025112100062 G80-3860LVAEU-17	CHERRY MX LOW PROFILE SPEED	khaki	RGB	EU (USA+ €-Symbol)
4025112106859 G80-3860LVAUS-17	CHERRY MX LOW PROFILE SPEED	khaki	RGB	US (USA)
4025112100017 G80-3860LYAEU-0	CHERRY MX LOW PROFILE RED	white	RGB	EU (USA+ €-Symbol)
4025112104756 G80-3860LYAKR-0	CHERRY MX LOW PROFILE RED	white	RGB	KR (Korea)
4025112106712 G80-3860LVADE-0	CHERRY MX LOW PROFILE SPEED	white	RGB	DE (Germany)
4025112100024 G80-3860LVAEU-0	CHERRY MX LOW PROFILE SPEED	white	RGB	EU (USA+ €-Symbol)
4025112106736 G80-3860LVAFR-0	CHERRY MX LOW PROFILE SPEED	white	RGB	FR (France)
4025112106750 G80-3860LVAGB-0	CHERRY MX LOW PROFILE SPEED	white	RGB	GB (United Kingdom)
4025112106699 G80-3860LVAUS-0	CHERRY MX LOW PROFILE SPEED	white	RGB	US (USA)

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.