

STREAM KEYBOARD TKL

The best STREAM ever – in a compact version without number pad



Models may vary from the image shown

For all lovers of quiet keyboards with the inimitable typing feel of a STREAM KEYBOARD, there is now a smaller and space-saving alternative: The STREAM KEYBOARD TKL. The two look very similar but differ in one significant way: The corded TKL version has the same main keypad as the popular STREAM KEYBOARD, but it does not have the number pad and is, therefore, smaller in size. For many applications, this is a decisive advantage.

One of the similarities between the two corded keyboards is an important product feature: CHERRY's own SX scissor technology. It is at the heart of the STREAM family and, at the same time, serves as the basic prerequisite for exacting and frequent typists to be able to work productively. The result is a perfect pressure point that ensures precise execution and super silent strokes of the keyboard.

The TKL version differs from its big brother in that the design has been shortened by omitting the number pad. The STREAM KEYBOARD TKL is perfect for those who hardly use the number pad but do not want to do without the familiar arrangement of the main keypad. The compact version saves space on the desk, both in the office and at home, making it easier to concentrate on the essentials. In the

industrial sector, this workhorse is ideal for 19-inch drawers due to its smaller dimensions. The WetEx® protective film lends itself to harsher working environments. It is specially tailored to the dimensions of the keyboard and is available as an accessory.

Anyone who spends a lot of time at their desk every day knows that an ergonomic sitting posture is essential to prevent certain health issues. Tension and pain in the back, hand, arm, and neck area can thus be avoided. It is, therefore, a huge plus point that the reduced dimensions of the small computer keyboard are accompanied by decisive ergonomic advantages. For right-handers, the mouse and keyboard are closer together. This means that the user keeps their arm closer to their side, which corresponds to an optimized working position and helps to avoid an incorrect posture. The German Social Accident Insurance (DGUV) confirms the theory that TKL keyboards promote a more natural and ergonomic posture.

The "Tested Safety" GS seal and the "Blue Angel" award promise further health benefits. The GS seal takes into account all relevant European directives and regulations that focus on protecting people's health. This includes, for example, that the letters stand out clearly from the keys. This is an important prerequisite for alleviating fatigue when working. The "Blue Angel" environmental protection label provides further guidance for responsible shopping. Anyone who buys products with this seal can be sure that high demands regarding environmental, health, and usage properties have been considered during product development. Furthermore, the STREAM KEYBOARD TKL does not contain any plastic packaging material.

In addition to the product features already mentioned, the CHERRY STREAM TKL also scores with many other interesting features. One of these is the status LEDs for CAPS LOCK and SCROLL LOCK. Since these are located directly in the key, time-consuming searches for activated status LEDs are a thing of the past. Although this feature is usually only found in higher price ranges, it is now standard for almost all CHERRY products. The flat corded keyboard functions according to the Plug&Play

principle. This means that it is ready for use without any driver installation. The practical six additional keys also prove useful in everyday life. You can use them to easily control multimedia applications without having to press an additional FN key. If you would like to add additional functions to your keys, you will find what you are looking for with the CHERRY KEYS software. It can be downloaded free of charge from www.cherry.de.

Do you spend a lot of time at your PC and are looking for a space-saving keyboard without a number pad? Do you also value high quality standards and want to make a positive contribution to your health? Then the STREAM KEYBOARD TKL is the right choice for you.

FUNCTION AND PERFORMANCE

- Space-saving design through omitting the numeric keypad
- Improved, ergonomic shoulder posture (due to shorter distance between keyboard and mouse)
- Alphanumeric section according to DIN ISO 9995-1
- 6 multimedia keys
- 2 integrated status displays for Caps Lock and Scroll buttons

TECHNICAL DATA

Weight main product:	24 oz
Dimensions product without packaging:	14,84 in x 6,42 in x 0,71 in
Cable-length:	5.91 ft
Storage temperature:	-4 °F - 140 °F
Working temperature:	32 °F - 104 °F
Product approvals:	<ul style="list-style-type: none"> • Blauer Engel • China RoHS • CE • FCC • GS • Windows Hardware Compatibility • UKCA

System Requirements-Hardware:	USB-A
Operating system:	<ul style="list-style-type: none"> • Windows 7 • Windows 8 • Windows 10 • Windows 11
Scope of delivery:	<ul style="list-style-type: none"> • Manual • Keyboard
Reliability:	MTBF > 80.000 Stunden
Software support:	CHERRY KEYS
USB dongle:	no
2.4 Ghz wireless connection:	no
Connection via Bluetooth:	no
Service life per key (in million strokes):	20 mio. actuations
Switching characteristics:	standard
Max. current consumption (mA) of keyboard:	20 mA
Keyboard format:	TKL (80%)
Integrated metal plate:	yes
Volume (dB) of keyboard:	49 db
N-key rollover:	not specified
Anti-ghosting:	not specified
Key encryption:	no
Internal memory:	no
Actuating force (cN):	65 cN
Actuating force tol.:	10 cN
Forward travel:	2,8 mm
Key stroke total travel path:	2,8 mm
Palm rest:	Palm rest not available
USB hub:	no
Special key functions:	<ul style="list-style-type: none"> • Next track • Play/Pause • Unmute/Mute • Volume up • Volume down • Last track
Illumination:	no

Adjustable feet:	integrated
Status LEDs:	in keys
Key technology:	Scissor
Keycap material:	ABS

Model number:	JK-85TKL
Warranty:	1 additional year voluntary limited manufacturers warranty

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

EAN & Part number	Color	Illumination	Layout
4025112097522 JK-8600BE-2	black	no	BE (Belgium)
JK-8600CE-2	black	no	
4025112097492 JK-8600CH-2	black	no	CH (Switzerland)
4025112097546 JK-8600CN-2	black	no	CN (China)
4025112097539 JK-8600CS-2	black	no	CS (Czech Republic / Slovak Republic)
4025112097454 JK-8600DE-2	black	no	DE (Germany)
4025112097577 JK-8600ES-2	black	no	ES (Spain)
4025112097485 JK-8600EU-2	black	no	EU (USA+ €-Symbol)
4025112097461 JK-8600FR-2	black	no	FR (France)
4025112097478 JK-8600GB-2	black	no	GB (United Kingdom)
4025112097515 JK-8600IT-2	black	no	IT (Italy)
4025112097508 JK-8600PN-2	black	no	PN (PanNordic)
4025112097560 JK-8600SL-2	black	no	SL (Slovenia)
4025112097553 JK-8600US-2	black	no	US (USA)
4025112097393 JK-8600BE-0	white-grey	no	BE (Belgium)
4025112097362 JK-8600CH-0	white-grey	no	CH (Switzerland)
4025112097416 JK-8600CN-0	white-grey	no	CN (China)
4025112097409 JK-8600CS-0	white-grey	no	CS (Czech Republic / Slovak Republic)
4025112097324 JK-8600DE-0	white-grey	no	DE (Germany)

EAN & Part number	Color	Illumination	Layout
4025112097447 JK-8600ES-0	white-grey	no	ES (Spain)
4025112097355 JK-8600EU-0	white-grey	no	EU (USA+ €-Symbol)
4025112097331 JK-8600FR-0	white-grey	no	FR (France)
4025112097348 JK-8600GB-0	white-grey	no	GB (United Kingdom)
4025112097386 JK-8600IT-0	white-grey	no	IT (Italy)
4025112097379 JK-8600PN-0	white-grey	no	PN (PanNordic)
4025112097430 JK-8600SL-0	white-grey	no	SL (Slovenia)
4025112097423 JK-8600US-0	white-grey	no	US (USA)

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.