

MW 2400

Provides easy to handle precision for any workplace



Models may vary from the image shown

With the 3 button CHERRY MW 2400 it makes no difference whether you are left-handed or right-handed. The modern design, the precise and thoroughly reliable technology, as well as multi-user capability guarantee uninterrupted professional work with reduced fatigue. Small details, such as the battery status indicator or the tiny Nano USB receiver, complete this well thought-out concept. CHERRY MW 2400 – further proof of typical CHERRY quality: reliable, high performance and lasting.

FUNCTION AND PERFORMANCE

- 3-button mouse, for both left-handed and right-handed operation
- Nano USB receiver
- GS approval
- Optical sensor technology (1,200 dpi)
- Battery status indicator on mouse
- Interference-free wireless 2.4 GHz technology (range of up to 10 meters / up to 33 ft)
- Operation for several mice (multi-station capability)
- Plug & Play via USB connection

TECHNICAL DATA

Weight main product:	3 oz
Dimensions product without packaging:	4,29 in x 2,44 in x 1,46 in
Weight of product incl. packaging (g):	3 oz
Dimensions product incl. packaging:	4,53 in x 2,76 in x 1,93 in
Content of master carton (pieces):	10
Weight of master carton incl. content (g):	47.27 oz
Dimensions master carton:	10.04 in x 6.1 in x 4.92 in
Storage temperature:	-4 °F - 149 °F
Working temperature:	32 °F - 122 °F
Max. Current consumption (mA)	75 mA
Mouse:	
Product approvals:	<ul style="list-style-type: none">• cULus• CE• FCC• Windows Hardware Compatibility• UKCA• RCM• China RoHS• GS
System Requirements-Hardware:	USB-A
Operating system:	<ul style="list-style-type: none">• Windows 7• Windows 8• Windows 10• Windows 11
Scope of delivery:	<ul style="list-style-type: none">• Manual• 1 x AA battery• Mouse• Nano-USB-Receiver
Reliability:	MTBF (90) > 80.000 Stunden
Switch type:	clicky
Number of keys:	3
Thumb buttons:	no
Max. resolution (dpi):	1.200 dpi

dpi switch:	no
Illumination:	no
Software support:	CHERRY KEYS
USB dongle:	yes
2.4 Ghz wireless connection:	yes
Encryption in wireless mode:	no
Wireless range (m):	33 ft
Connection via Bluetooth:	no
Encryption in Bluetooth mode:	no
Number of batteries:	1

Battery type:	Alkaline
Battery design:	AA
Battery rechargeable:	no
Battery replaceable:	yes
Battery charging socket:	no
Model number:	JF-07
Warranty:	2 years warranty

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

Actual battery life is strongly depending on individual user behavior and hardware setup.

EAN & Part number	Color	Illumination	Country version
4025112088520 JW-0710-2	black	no	Europe / USA
4025112093104 JW-0711-2	black	no	Asia

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.