

MW 8C ERGO

When you place high demands on your ergo-nomic wireless mouse



Models may vary from the image shown

Uncompromising quality, exquisite design, the very latest technology and the finest materials: These are the ingredients of the CHERRY MW 8C ERGO wireless mouse. The large, ergonomic form is designed for use with the right hand. Even after hours of intensive work, it still sits comfortably on the mouse. Mouse buttons made of anodised aluminum pamper the hand with their pleasant feel. Comfort is underlined with rubber-padded side sections, with thumb-rest and trendy Voronoi pattern. The thumb automatically finds a pleasant position and can rest relaxed. Large gliding surfaces allow the mouse to move lightly over the desktop, relieving stress from the wrist.

The high-precision sensor allows the wireless mouse to be used on nearly every surface, even on glass tables. Press the DPI button to set the resolution to any of the 4 levels 600, 1000, 1600 or 3000 dpi. This means the mouse is ready for use with high-resolution 4k monitors. The installed rechargeable lithium battery can be simply charged with the supplied USB C cable – even while you work. The generous capacity of 550 mAh means that one charge is enough for several weeks of uninterrupted productivity. A two-colour status LED provides the user with information on the battery status, the charging status, the selected resolution

or the connection status. Unlike a conventional mouse, the CHERRY MW 8C ERGO can be connected with either the 2.4 GHz wireless USB receiver or Bluetooth® and you can change connection types quickly using a switch on the base of the mouse. This allows e.g. a laptop to be connected via Bluetooth® and a PC to be connected via a regular wireless connection and both to be operated with the same mouse. Simply press the switch to switch between the two devices. In both cases, the data is transmitted with AES-128 en-ryption and a long range of 10 meters.

In addition to this, the CHERRY MW 8C ERGO has a number of other impressive features and subtle details. A highly durable metal mouse wheel, a storage pocket with magnetic latch for the USB receiver as well as a velvety transport pouch. The attention to detail of this wireless mouse leaves nothing to be desired and it is equally suitable for mobile and stationary applications.

FUNCTION AND PERFORMANCE

- Superior handling, especially for right-handed users
- Ideal for medium-sized to large hands
- Thumb rest for fatigue-free working
- Metal surface and mouse wheel
- Rubber-padded sides with trendy Voronoi pattern
- Optionally connected using Bluetooth® or a 2.4 GHz wireless unit – both with AES-128 encryption.
- Highly precise sensor with resolution adjustable in four stages up to 3,000 dpi
- Works on nearly all surfaces, including glass
- Status LED shows low residual battery charge, charging status and resolution
- Lithium battery can be charged via USB-C
- Extra-small nano receiver for wireless operation
- 6 buttons and a scroll wheel
- Includes practical transport pouch

TECHNICAL DATA

Weight main product:	4 oz
Dimensions product without packaging:	4,72 in x 3,11 in x 1,75 in
Storage temperature:	5 °F - 140 °F
Working temperature:	32 °F - 104 °F
Max. Current consumption (mA) Mouse:	10 mA
Product approvals:	<ul style="list-style-type: none"> • BQB • CE • China RoHS • FCC • UKCA • Windows Hardware Compatibility
System Requirements-Hardware:	<ul style="list-style-type: none"> • Bluetooth 4.0 or higher • USB-A
Operating system:	<ul style="list-style-type: none"> • Windows 7 • Windows 8 • Windows 10 • Windows 11
Scope of delivery:	<ul style="list-style-type: none"> • Manual • Mouse • Nano-USB-Receiver • USB-A to Micro-USB Cable • Pouch
Switch type:	clicky
Number of keys:	6
Thumb buttons:	yes
Max. resolution (dpi):	3.000 dpi

dpi switch:	yes
dpi levels:	4
Illumination:	no
Software support:	CHERRY KEYS
USB dongle:	yes
2.4 Ghz wireless connection:	yes
Encryption in wireless mode:	yes
Wireless range (m):	33 ft
Connection via Bluetooth:	yes
Encryption in Bluetooth mode:	yes
Bluetooth protocol:	Bluetooth 4.2
Bluetooth range (m):	33 ft
Number of batteries:	1
Battery type:	Li-Ion
Battery design:	Special
Battery rechargeable:	yes
Battery replaceable:	no
Battery charging socket:	USB-C
Model number:	JF-86
Warranty:	1 additional year voluntary limited manufacturers warranty

Errors, technical changes and delivery options reserved. Technical information refers only to the specification of the products. Properties are not guaranteed.

Actual battery life is strongly depending on individual user behavior and hardware setup.

EAN & Part number	Color	Illumination	Country version
4025112095702 JW-8600	black/silver	no	Europe
4025112097317 JW-8600US	black/silver	no	USA
4025112096471 JW-8601	black/silver	no	Asia

Please contact your local CHERRY service and support teams or your CHERRY sales partners for versions available in your country.